

TCB Threaded Busbar With Fixing Hole



FEATURES

End holes can be used to fix busbar to a support or connect the main input conductor

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

Material: Copper




SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Width (W)	Thickness (T)	Length (L)	Hole Size (HS)	Thread Size (TS)
TCB20X10-1M	550290	0.79"	0.39"	39.37"	0.39"	M8
TCB30X10-1M	550180	1.18"	0.39"	39.37"	0.39"	M8
TCB30X10-2M	550160	1.18"	0.39"	78.74"	0.39"	M8

Table 2/2

Catalog Number	Article Number	Torque (TQ)	A	Unit Weight
TCB20X10-1M	550290	24 ft·lbf	0.98"	3.68 lb
TCB30X10-1M	550180	24 ft·lbf	0.98"	5.51 lb
TCB30X10-2M	550160	24 ft·lbf	0.98"	11.9 lb



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

