

Inner Doors, ADIS

Displays and indicators can be mounted, on a surface within the enclosure while covering other components, and preventing unauthorized access.

FEATURES

Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening (Machining is required). Double-bit 3 mm lock, 800 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm, adjustable depth position with AMG accessory. Workable area: H-55, W-108. 19" version available on request.

Material: Door 1.5 mm AISI 304 stainless steel and vertical top and bottom profiles 2 mm, AISI 304 stainless steel.

Protection: IP 2XC.

Finish: 400 pre-grained stainless steel.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

Material: Stainless Steel 304

Finish: Brushed

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Door Size	Latch Quantity	Product Family
ADIS04030	15.75in	11.81in	0.59in	13.58 x 7.56in	1	Wall Mounted
ADIS05040	17.52in	11.5in	0.59in	17.52 x 11.5in	1	Wall Mounted
ADIS05050	17.52in	15.43in	0.59in	17.52 x 15.43in	1	Wall Mounted
ADIS06040	21.46in	11.5in	0.59in	21.46 x 11.5in	1	Wall Mounted
ADIS06060	21.46in	19.37in	0.59in	21.46 x 19.37in	1	Wall Mounted
ADIS08060	29.33in	19.37in	0.59in	29.33 x 19.37in	2	Wall Mounted
ADIS10080	37.2in	27.24in	0.59in	37.20 x 27.24in	2	Wall Mounted
ADIS12080	45.08in	27.24in	0.59in	45.08 x 27.24in	2	Wall Mounted

ADDITIONAL PRODUCT DETAILS

To order 19"version, please add I19 to the catalogue no, e.g. ADIS04030I19. Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.