

ProLine G2 Industrial Seismic Packages

nVent HOFFMAN ProLine G2 Seismic Industrial Packages are fully-configured solutions capable of withstanding Zone 4 seismic activity with a panel load of 1,000 lbs. (454 kg), with no degradation to structural integrity or functional performance. For convenience, a single part number includes a frame, solid single door, key-locking handle, solid top, solid rear cover, solid side covers, full mounting subpanel, gland plate, 100-mm fully-sealed base, lifting eyes, and a number of other structural components. Note: for specific application questions consult the factory.

INDUSTRY STANDARDS

UL 508A Listed 508; Type 12; File Number E61997
cUL Listed per CSA C22.2 No. 94; Type 12; File No. E61997
NEMA/EMAC Type 12
CSA File Number 42186; Type 12
IEC 60529, IP55
Telcordia Technologies' Earthquake Environment Criteria GR-63-CORE
Zone-4 Capable with panel-load of 1,000 lbs (454 kg)

FEATURES

12-gauge (2.5 mm) roll-formed steel with welded corners, and hybrid frame profile for superior performance under load

Consistent with Type-12 Industrial Packages, but reinforced in all directions using seismically capable components/accessories to withstand forces present in seismic areas with a Zone-4 risk assignment

Frame features a 25-mm DIN standard, alternating rectangular and round hole pattern

Single door includes robust 3-point latch system to maintain door closure during seismic activity, with gussets included at the top and bottom of the door to increase rigidity

Seamless Polyurethane gasket provides a water-tight, dust-tight seal against moisture and contaminants

Door bar system and two grounding studs present

Single door left-hinged standard, with Key-locking Flush Swing Handle standard

Galvanized Duro-Stand gland plate included

100-mm Fully-Sealed Base with seismic mounting into frame's welded steel corners

Seismic Floor Mounting Brackets supplied loose for affixing enclosure to floor

White painted full subpanel fully recessed in rear-most mounting position: EZ-Load Glide Blocks supplied only in the front to support rear-most subpanel position

Top and bottom panel brackets, panel support brackets (side), and panel wedges to secure a populated subpanel are incorporated in the design

Gussets mounted to the frame's door opening at the top and bottom

White painted partial subpanels at top and bottom of frame's sides, unique seismic design

Depth-mounted 3-row Grid Strap at mid-point of frame

Solid Side Covers included standard

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Thickness	Max Subpanel Size
P2K1888S	36207	70.94in	31.8in	31.69in	14ga	67.2 x 28.7in
P2K2088S	36211	78.82in	31.8in	31.69in	14ga	75.0 x 28.7in
P2K20108S	36212	78.82in	39.68in	31.69in	14ga	75.0 x 36.5in
P2K18108S	36208	70.94in	39.68in	31.69in	14ga	67.2 x 36.5in

ADDITIONAL PRODUCT DETAILS

HxWxD are nominal height, width and depth dimensions.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE