

Controlador PXI Express, 4 HP, I3-1115G4E 16-512

NÚMERO DE CATÁLOGO

21265-120



El controlador integrado nVent SCHROFF PXIe es el controlador integrado 3U de una ranura más compacto y potente para las plataformas PXI Express y CPClexp. Con sus capacidades de interfaz enormes y preparadas para el futuro, funciona perfectamente con la mayoría de las aplicaciones de prueba y medición. El Controller está impulsado por una 11.ª generación de procesadores Intel® Core? I3 / i5 combinados con hasta 64 GB de memoria DDR4 y admite fácilmente aplicaciones de alto ancho de banda con interconectividad de sistema PCIe Gen4 y dual 2500BASE-T preparados para el futuro.

CARACTERÍSTICAS

Controlador de Sistema PXI Express, 3 U, 4 HP, con procesador Intel Core I3-1115G4E

PXI?-5 PXI Express hardware spec. Cumplimiento Rev.2,0

Máximo 14 Gb/s de ancho de banda PCIe

Almacenamiento actualizable m.2 NVMe y DDR4

3x USB3.1, 2x GbE y 1x DP 1,2 en el panel frontal

Completo personalizable AMI Aptio® Embedded BIOS

ATRIBUTOS DEL PRODUCTO

Tipo de producto: Sistema

Tipo: Controlador

Transferencia de datos: PCIe Gen3

Altura del rack: 3U

De conformidad con: PXISA PXI-5 R1.1

Fondo: 160mm

Peso bruto: 0.548kg

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Conforme a PICMG rev. 3,0 y PXI-5.

Controladores modificados disponibles bajo petición.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE