


# Placa trasera de alimentación CPCI con conector P 47, 3 U, 16 HP, 2x P47

## NÚMERO DE CATÁLOGO

**23098-394**

Power Backplane para aplicaciones CompactPCI. Con el conector de alimentación P47.



## CARACTERÍSTICAS

De conformidad con: PICMG 2,11 R1.0 CompactPCI Power Interface Especificación

De conformidad con: PICMG 2,9 R1.0 Especificación de bus de gestión de sistemas

Operación única, paralela o redundante posible

Dirección geográfica ajustable

Fuente de alimentación sobre contactos de crimpado insertados en el enchufe, sin voltaje de alimentación en el backplane

Cable de alimentación disponible como accesorio

Tomacorrientes DC con powerbugs para caídas de voltaje extremadamente bajas

Can be switched in parallel, PSU status signals FAL# and DEG# # and DEG#can be read out separately



## ATRIBUTOS DEL PRODUCTO

Tipo de producto: Plano trasero

Número de ranuras: 2

Altura del rack: 3U

Tipo de panel posterior: Backplane CompactPCI Power con P47

Ancho de ranura: 8HP

Tipo de conector: P47

Tipo de conector de alimentación: (2) P47

Tipo de conector de servicios: SMCQ, 12 pines; MicroMatch, 10 pines

Anchura: 80.3mm

Peso neto: 0.322kg

Cantidad del paquete: 1

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

