

Kit de Panel Frontal, Blindado, Inferior Bisagra, 3 U, 42 HP, 2,5 mm, AL, Anodizado Frontal, Conductor Trasero



NÚMERO DE CATÁLOGO

20848-599

Panel frontal en U-perfil inferior con bisagras para junta textil.

CARACTERÍSTICAS

El panel frontal del perfil en U se puede desdoblar a un ángulo de apertura de 135° (no RatiopacPRO)

Permite el montaje en rieles horizontales

Blindado, panel frontal U con junta textil EMC

Adecuado para subracks (EuropacPRO) y cajas (RatiopacPRO, PropacPRO, CompacPRO)



ATRIBUTOS DEL PRODUCTO

Altura del rack: 3U

Tipo de accesorio: Panel frontal

Ancho del rack: 42HP

Cantidad del paquete: 1

Montaje: Con bisagras, abajo

Tipo de junta: Textil EMC

Acabado frontal: Anodizado

Acabado trasero: Conductor

Bordes tratados: No

De conformidad con: IEC 60297-3-101; IEEE 1101.1/10

Fondo (D): 2.5mm

Apantallamiento EMC: No (Retrofitable)

Acabado: Anodizado; Pasivado

Altura (H): 128.4mm

Tipo de producto: Panel frontal

Anchura (W): 213mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

El panel frontal se puede quitar en posición abierta ($> 135^\circ$).

Technical drawing of a rectangular plate with the following dimensions and features:

- Overall width: A
- Overall height: H
- Top edge features:
 - Left corner: 7.45 (horizontal) and 3 (vertical)
 - Right corner: 3 (horizontal) and $M2.5$ (vertical)
- Internal features:
 - Top edge: C (distance from right corner to start of cutout)
 - Bottom edge: D (distance from left corner to start of cutout), $B - 25.4$ (total width of cutout area), and 3.1 (width of cutout)
 - Left edge: 15.6 (distance from bottom corner to start of cutout), 16 (width of cutout), and 8.2 (height of cutout)
- Material and finish: $\phi 5.9 \times 3.3$ (top left corner), $M2.5$ (bottom right corner)
- Section lines: $X-X$ (horizontal) and $Y-Y$ (vertical)

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Straubenhardt, Germany
 +49.7082.794.0
 Betschdorf, France
 +33.3.88.90.64.90
 Warsaw, Poland
 +48.22.209.98.35
 Assago, Italy
 +39.02.932.7141
 Chat with us:
nvent.com/schroff

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Este documento es generado por el sistema.