

Sistema PXI con alimentatore ATX, 4 U, 8 slot, 44 CV

CODICE A CATALOGO

14579-008

Chassis PXI per sistemi desktop con gabbia per schede verticali per otto schede da 3 U e alimentatore integrato.

CARATTERISTICHE

Sistema conforme a IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11); backplane conforme a PICMG rev. 3,0 e PXI 2,0

Chassis desktop PXI, 4 U, 44 HP con alloggiamento per schede verticale. Formato scheda anteriore: 3U, 160 mm

Backplane, 8 slot, 3 HE, 64 bit, slot di sistema sinistro

Dissipazione del calore con flusso d'aria dal basso verso la parte posteriore

Alimentatore ATX da 400 W, ingresso c.a. ad ampia gamma con interruttore di alimentazione sul retro

Backplane con commutazione clock interna/esterna



ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Sistema

Numero di scanalature: 8

Tipo: Desktop

Tipo di backplane: 3 U CompactPCI con PXIbus

Trasferimento dati: Bus PCI a 64 bit

Potenza per slot: 30W

Tensione di ingresso CA: 100 – 240V

Direzione del flusso d'aria: Dal basso sul retro

Altezza del rack: 4U

Tipo di alimentazione: Telaio aperto

Alimentazione inclusa: Sì

I/O posteriore: N.

È conforme a: PXISA PXI-1 R2.0

Profondità: 355mm

Peso netto: 9.6kg

Quantità nella confezione: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Sistemi modificati disponibili su richiesta.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE