

Controller PXI Express, 4 te, W-11865MLE 32-1024



CODICE A CATALOGO

21265-170

Il controller integrato nVent SCHROFF PXIe è il controller integrato 3 U/4 HP più compatto e potente per piattaforme PXI Express e CPCIexp. Grazie all'interfaccia completa e a prova di futuro e alle capacità di potenza di calcolo, è ideale per applicazioni di test e misurazione. Il controller è basato su un processore Intel® Xeon® di 11a generazione, combinato con fino a 64 GB di memoria DDR4 e supporta applicazioni a larghezza di banda elevata con interconnettività PCIe Gen4 e 10GBASE-T.

CARATTERISTICHE

Controller di sistema PXI Express, 3 HE, 4 te, mit Intel-Prozessor W-11865MLE

Specifiche hardware PXI?-5 PXI Express Conforme alla Rev.2,0

Larghezza di banda PCIe massima di 28 GB/s.

Storage m.2 e DDR4 aggiornabile

2 USB3.1, 2 10 GbE e 1 DP 1,2 sul pannello anteriore

BIOS integrato AMI Aptio® completamente personalizzabile

ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Sistema

Tipo: Controller

Trasferimento dati: PCIe Gen3

Altezza del rack: 3U

È conforme a: PXISA PXI-5 R1.1

Profondità: 160mm

Peso lordo: 0.562kg

Quantità nella confezione: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products

may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Conforme a PICMG rev. 3,0 e PXI-7.

Controller modificati disponibili su richiesta.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

