

401 Clevis Hanger



FEATURES

Recommended for the suspension of stationary non-insulated pipe lines

Flared edges help prevent sharp surfaces from coming into contact with the pipe (1/2" to 2" pipe sizes)

Clevis bottom pivots to allow pipe to be fed from either direction

Conforms with Federal Specification WW-H-171 (Type 1), Manufacturers Standardization Society (MSS) SP-58 (Type 1)

Material: Steel
Finish: Electrogalvanized; Pregalvanized



SPECIFICATIONS

Table 1/2



Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A	B
4010050EG	179398	15	21 mm	M10	59 mm	29 mm
4010075EG	179399	20	27 mm	M10	64 mm	32 mm
4010100EG	179420	25	34 mm	M10	71 mm	35 mm
4010125EG	179421	32	43 mm	M10	80 mm	40 mm
4010150EG	179422	40	48 mm	M10	94 mm	53 mm
4010200EG	179423	50	60 mm	M10	110 mm	63 mm
4010250EG	179424	65	76 mm	M12	134 mm	78 mm
4010300EG	179425	80	89 mm	M12	154 mm	90 mm
4010350EG	179521	90	101.6 mm	M12	172 mm	101 mm
4010400EG	179426	100	114 mm	M16	189 mm	111 mm
4010500EG	179427	125	140 mm	M16	231 mm	130 mm
4010600EG	179428	150	165 mm	M20	268 mm	153 mm

Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A	B
4010800EG	179429	200	219 mm	M20	356 mm	204 mm
4011000EG	179430	250	273 mm	M20	419 mm	230 mm
4011200EG	179431	300	324 mm	M20	473 mm	258 mm

Table 2/2

Catalog Number	Article Number	C	Static Load	Certifications
4010050EG	179398	9 mm	2700N	cUL, ITB, UL
4010075EG	179399	9 mm	2700N	cUL, UL, ITB
4010100EG	179420	9 mm	2700N	cUL, UL, ITB
4010125EG	179421	9 mm	2700N	ITB, cUL, UL
4010150EG	179422	17 mm	2700N	ITB, cUL, UL
4010200EG	179423	22 mm	2700N	UL, ITB, cUL
4010250EG	179424	25 mm	5000N	UL, cUL, ITB
4010300EG	179425	29 mm	5000N	UL, cUL, ITB
4010350EG	179521	34 mm	5000N	UL, cUL
4010400EG	179426	35 mm	5000N	ITB, UL, cUL
4010500EG	179427	41 mm	6400N	ITB, cUL, UL
4010600EG	179428	48 mm	8600N	UL, ITB, cUL
4010800EG	179429	80 mm	8900N	ITB, cUL, UL
4011000EG	179430	66 mm	16000N	ITB
4011200EG	179431	78 mm	17000N	ITB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

