

SpectraCool Slim Fit-airconditioning voor binnen - EMEA



S06
1000/1700 BTU/Hr.
300/500 Watt

S10
3400/5000 BTU/Hr.
1000/1500 Watt

S16
6800/8500/13500 BTU/Hr.
2000/2500/4000 Watt

SpectraCool SlimFit Air Conditioners are designed with three space-saving mounting options to maximize footprint. They have been developed to meet the requirements of worldwide industrial customers, easy to specify and easy to use. From filterless operation to global certifications, the SpectraCool Slim Fit Air Conditioner makes automation cooling easy for system designers and operations maintenance teams around the world.

Select units come with a Commboard for Remote Access Control (RAC), an integrated, parametric controller designed to work seamlessly with our enclosure air conditioner units for the purpose of remotely monitoring and managing anywhere from a single unit to an entire network of Spectra cool air conditioners from virtually anywhere in the world with a secure internet connection. Ensure that your systems are always running at optimal temperature levels, increase productivity and improve overall system reliability.

INDUSTRIENORMEN

UL/cUL Listed Type 12; File No.SA6453

CE, EAC, RoHS

Cooling performance tested by TÜV SÜD Germany, according to DIN EN 14511

IP 54 internal loop, IP 34 external loop

KENMERKEN

Les unités de contrôle d'accès à distance peuvent contrôler jusqu'à 2 capteurs de température et 10 alarmes. Ils peuvent contrôler plusieurs protocoles de communication : SNMP, Modbus TCP, Ethernet/IP et Profinet.

Slim Fit Design with three mounting options; fully recessed, partial recessed and surface mount

Aesthetic design plastic cover to optimize air flow

R134a refrigerant

Voltage: 230 V (50/60 Hz), 115 V (50/60 Hz) and 400/460 V 3-phase (50/60 Hz)

Operating temperature range from 50 F / 10 C to 131 F / 55 C

Easy filter replacement for extremely dusty environments

Dust resistant coils for filterless operation

Active condensate management to prevent dripping water

Energy efficient rotary compressor

Terminal block power input

Standard cutout dimension for easy exchange

Every unit functionally tested before shipping

Standard Air Conditioners are compatible with an enclosure door switch

Mounting hardware, gaskets and user manual furnished with the unit

Kleur: Lichtgrijs
Afwerking: Gepoedercoat
Kleurcode: RAL 7035

SPECIFICATIES

Catalogusnummer	Nominale capaciteit watt	Nominale capaciteit BTU/u	Nominale spanning	Aantal fasen	Koelmiddel	Materiaal
S162526G031	2500W	8500Btu/h	230V	1	R134a	Plaatstaal
S060316G031	300W	1000Btu/h	115V	1	R134a	Plaatstaal
S101526G031	1500W	5000Btu/h	230V	1	R134a	Plaatstaal
S101016G031	1000W	3400Btu/h	115V	1	R134a	Plaatstaal
S060516G031	500W	1700Btu/h	115V	1	R134a	Plaatstaal
S101026G031	1000W	3400Btu/h	230V	1	R134a	Plaatstaal
S060526G031	500W	1700Btu/h	230V	1	R134a	Plaatstaal
S060326G031	300W	1000Btu/h	230V	1	R134a	Plaatstaal
S162026G031	2000W	6800Btu/h	230V	1	R134a	Plaatstaal
S101516G031	1500W	5000Btu/h	115V	1	R134a	Plaatstaal
S101046G031	1000W	3400Btu/h	460V	1	R134a	Plaatstaal
S101546G031	1500W	5000Btu/h	460V	3	R134a	Plaatstaal
S162546G031	2500W	8500Btu/h	460V	3	R134a	Plaatstaal
S162046G031	2000W	6800Btu/h	460V	3	R134a	Plaatstaal
S164046G031	4000W	13500Btu/h	460V	3	R134a	Plaatstaal

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Ons krachtige merkenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE