

Ingebouwd rek 3 u, 84 pk

CATALOGUSNUMMER

10170-014

Geschikt voor voortdurende trillingen, schokken, hoge temperaturen en hoge vochtigheid.

KENMERKEN

Voor mobiele spoorwegaanpassingen

Geschikt voor voortdurende trillingen, schokken, hoge temperaturen en hoge vochtigheid

Geschikt voor 1, 2 of 3 u SNCF subracks (NF F61-005, CF 60-002)


De achterzijde is uitgerust met standaardconnectoren; de dwarsbalk kan worden gecodeerd voor de SNCF-codeerpennen

Dwarsbalk met geïntegreerd kabelkanaal

Meerdere rekken kunnen worden gestapeld of in rijen worden gemonteerd

Geproduceerd volgens een lasproces, gecertificeerd volgens en 15085 (CL2)

Roestvrijstalen lassen gepassiveerd om corrosie te voorkomen



PRODUCTKENMERKEN

Productserie: Ingebouwd rek

Rekhoogte: 3U

Hoogte: 156.7mm

Rekbreedte: 84HP

Breedte: 496.4mm

Hoeveelheid in verpakking: 1

Voldoet aan: SNCF NFF 61005; SNCF NFF 60002

Diepte: 341.8mm

Framemateriaal: Staal

Materiaal: Roestvrij staal

Producttype: Rek

Statische belasting: 25kg

Brutogewicht: 4.35kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ons krachtige merkenportfolio:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE