

# Horizontale rail, voorzijde, Type R-LD, robuust, lange lip , 20 pk



Combinations of horizontal rails and side panels

|                 | Light r-L | Plastic r-L | Heavy r-L | Plastic r-R |
|-----------------|-----------|-------------|-----------|-------------|
| Heavy r-L       | -         | +           | +         | +           |
| Heavy r-R       | +         | +           | +         | +           |
| Light r-L       | +         | +           | +         | +           |
| Horizontal rail | +         | +           | +         | +           |

Legend: + = can be combined, - = combination not recommended

## CATALOGUSNUMMER

**34566-320**

De robuuste horizontale rail is bestand tegen schokken en trillingen tot 25 g. het maakt het gebruik van IEEE-handgrepen mogelijk.

## KENMERKEN

Type R-LD „robuuste” horizontale rails met bevestiging met 3 gaten voor extra robuustheid

Voor het inbrengen/uittrekken van CompactPCI- of VME64x-kaarten

Met HP-eenheden afgedrukt vanaf 28 pk

Lengte 20, 28, 40, 42, 63, 84 pk of 1000 mm

Aluminium extrusie, geanodiseerde afwerking, geleidend contactoppervlak, met HP markeringen



## PRODUCTKENMERKEN

Rekbreedte: 20HP

Hoeveelheid in verpakking: 1

Afwerking: Geanodiseerd

Lengte: 106.68mm

Materiaal: Aluminium

Productserie: EuropacPRO

Producttype: Horizontale rail

Type: Robuust, LD

Werkt met: Subracks

Nettogewicht: 0.03kg

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## WAARSCHUWING

---

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

