


Panheadschroef, Pozidriv



Panhead schroef, Pozidrive.

KENMERKEN

Panhead schroef, pozidrive

Pozidriv has a set of 45° radial indentations from the main cross recess leading to 4 additional contact points and greater stabilization to provide a greater contact surface. As a result, it decrease cam-out and wear, which allows greater torque to be applied.

Materiaal: Staal
Producttype: Schroef



SPECIFICATIES

Table 1/2

Catalogusnummer	Diameter	Lengte	Afwerking	Hoeveelheid in verpakking	Schroefdraadmaat	Productserie
21100-788		12mm	Verzinkt	100	M5	EuropacPRO
21120-150	5mm	10mm	Verzinkt	100	M5	
21101-222		16mm	Vernikkeld	100	M2.5	Plug-in-eenheid frametype
21101-221		12mm	Vernikkeld	100	M2.5	Plug-in-eenheid frametype
21101-220		10mm	Vernikkeld	100	M2.5	Plug-in-eenheid frametype
21101-219		6mm	Vernikkeld	100	M2.5	Plug-in-eenheid frametype
21102-024	3mm	6mm	Verzinkt	100	M3	
21100-021	6mm	16mm	Verzinkt	50	M6	EuropacPRO, RatiopacPRO, RatiopacPRO air, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21100-022	6mm	16mm	Verzinkt	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO air, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO
21101-314		5mm	Vernikkeld	100	M2.5	
21100-650	6mm	16mm	Zinc Plated, Black	100	M6	EuropacPRO, RatiopacPRO, RatiopacPRO air, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO

Catalogusnummer	Diameter	Lengte	Afwerking	Hoeveelheid in verpakking	Schroefdraadmaat	Productserie
21101-069		8mm	Vernikkeld	100	M2.5	Plug-in-eenheid frametype
21120-202	6mm	16mm	Verzinkt	50	M6	
21120-203	6mm	16mm	Verzinkt	100	M6	

Table 2/2

Catalogusnummer	Type	Werkt met	Schroefdraadlengte	Type schroefdraad	Certificeringen
21100-788	Panheadschr oef	Subracks	12mm		RoHS
21120-150	Coderingsbl ok	Behuizing	10mm		RoHS
21101-222	Panheadschr oef	Achterplaten, Testadapters	16mm		RoHS
21101-221	Panheadschr oef	Achterplaten, Testadapters	12mm		RoHS
21101-220	Panheadschr oef	Achterplaten, Testadapters	10mm		RoHS
21101-219	Panheadschr oef	Achterplaten, Testadapters	6mm		RoHS
21102-024	Panheadschr oef		6mm	Metrisch	RoHS
21100-021	Panheadschr oef	Frontpanelen, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21100-022	Panheadschr oef	Frontpanelen, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21101-314	Panheadschr oef	Achterplaten, Testadapters	5mm		RoHS
21100-650	Panheadschr oef	Frontpanelen, Eurorack, Novastar, Varistar, Varistar CP	16mm		RoHS
21101-069	Panheadschr oef	Achterplaten, Testadapters	8mm		RoHS
21120-202	Panheadschr oef	Frontpanelen, Eurorack, Novastar, Varistar, Varistar CP	16mm		
21120-203	Panheadschr oef	Frontpanelen, Eurorack, Novastar, Varistar, Varistar CP	16mm		

WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk

letsel en de dood en/of uw garantie ongeldig maken.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. Alle nVent-merken en -logo's zijn eigendom van of in licentie gegeven door nVent Services GmbH of haar gelieerde ondernemingen. Alle andere handelsmerken zijn het eigendom van hun respectieve eigenaren. nVent behoudt zich het recht voor om specificaties zonder kennisgeving te wijzigen.

Dit document is door het systeem gegenereerd.