

Hol-Sealers Hole Seal

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals. Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.



BRANSJESTANDARDER

UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)

Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66

FUNKSJONER

Oljebestandig pakning følger med

Available in multiple colors and sizes

Steel model has plated stud (10-32x5/8) and wing nut

Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

SPESIFIKASJONER

Table 1/2

Katalognummer	Materiale	Overflate	Farge	Fargekode	Tykkelse	Hulldiameter
AS050	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	22mm max
AS050SS	Rustfritt stål 304	Pusset			1.5mm	22mm max
AS050LG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	22mm max

Katalognummer	Materiale	Overflate	Farge	Fargekode	Tykkelse	Hulldiameter
AS056CB	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	14mm max
AS056M	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	14mm max
AS056MFB	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	14mm max
AS056MLG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	14mm max
AS056MSS	Rustfritt stål 304	Pusset			1.5mm	14mm max
AS075	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	27mm max
AS075LG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	27mm max
AS075SS	Rustfritt stål 304	Pusset			1.5mm	27mm max
AS100	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	35mm
AS100LG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	35mm
AS100SS	Rustfritt stål 304	Pusset			1.5mm	35mm
AS125	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	43mm max
AS125LG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	43mm max
AS125SS	Rustfritt stål 304	Pusset			1.5mm	43mm max
AS150	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	51mm max
AS150LG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	51mm max
AS150SS	Rustfritt stål 304	Pusset			1.5mm	51mm max

Table 2/2

Katalognummer	Materiale	Overflate	Farge	Fargekode	Tykkelse	Hulldiameter
AS200	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	64mm max
AS200LG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	64mm max
AS200SS	Rustfritt stål 304	Pusset			1.5mm	64mm max
AS250	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	76mm max
AS250SS	Rustfritt stål 304	Pusset			1.5mm	76mm max
AS300	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	92mm max
AS300SS	Rustfritt stål 304	Pusset			1.5mm	92mm max
AS350	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	105mm max
AS350SS	Rustfritt stål 304	Pusset			1.5mm	105mm max
AS400	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	117mm max
AS400SS	Rustfritt stål 304	Pusset			1.5mm	117mm max
ASPB	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	32mm max
ASPBG	Lakkert stål	Pulverbelagt	Grå	ANSI 61	1.5mm	22mm max
ASPBSS	Rustfritt stål 304	Pusset			1.5mm	22mm max
ASPBGLG	Lakkert stål	Pulverbelagt	Lys grå	RAL 7035	1.5mm	32mm max
ASPBSS	Rustfritt stål 304	Pusset			1.5mm	32mm max

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



©2026 nVent. Alle nVent-merker og -logoer er eid eller lisensiert av nVent Services GmbH eller dets datterselskaper. Alle andre varemerker eies av de respektive eierne. nVent forbeholder seg retten til å endre spesifikasjonene uten forvarsel.

Dette dokumentet er systemgenerert.