

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC, 2100H 600W 600D

KATALOGNUMMER

10630-048



Kabinett med IP 55 og EMC-samsvar for ekstreme seismiske miljøer testet til Bellcore sone 4 med en dynamisk lastekapasitet på 500 kg. Tilpassede løsninger med høyere lasting er tilgjengelige. Kabinettet er mye brukt i IKT-applikasjoner i jordskjelvutsatte områder, konstruksjons- og skipsfartsfasiliteter, flyplasser, jernbaner og mange flere.

Andre dimensjoner og versjoner kan konfigureres i den nettbaserte konfiguratoren

FUNKSJONER

Jordskjelv sikker opp til Bellcore Zone 4, testet med 500 kg per Telcordia GR-63 Core, NEB sertifisert

Statisk belastning/bæreevne 1600 kg.

Type beskyttelse IP55

Høy skjermingskapasitet testet i henhold til IEC 61587-3, med EN4545-2 brannsikkerhetspakning

PRODUKTEGENSKAPER

Produkttype: Skap

Produktserie: Varistar CP

Rammemateriale: Stål

Overflate: Pulverbelagt

Rackhøyde: 42U

Høyde: 2000mm

Bredde: 600mm

Dybde: 600mm

Statisk belastning: 1600kg

Beskyttelsesgrad: IP55

Samsvarer med: IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-3; IEC 61587-1; IEC 61587-2; EN 45545-2; Telcordia GR-63 Core Zone 4

Farge: Svart grå

Fargekode: RAL 7021

Frekvens: 50 Hz

Materiale: Stål

Nettovekt: 180.164kg

Antall pakker: 1

Støt- og vibrasjonstoleranse: 5g (force)

Fungerer med: Varistar CP

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE