

PXI-Express-system, 4 U, 18 slisser, Gen 3

KATALOGNUMMER

14579-040

Stasjonær PXI Express-chassis for én PXI-ettrykkssystemkontroller med opptil 16 HP og 17 PXI- eller PXI Express-kort med bredde på 4 hk.

FUNKSJONER

PXI Express Desktop chassis, 4 U, 84 HP, med håndtak og 19? Monteringsbraketter

1 PXI Express System Slot med 16 HP bredde, 1 PXI Express timing Slot og 16 Hybrid Slots

Svært høy ytelse Gen 3 PCIe-bytte med en standard fire-link (4x4) systemspor

Kraftig kjølekonsept med lav viftestøy, 50 W per spor ved 15K temperaturøkning

Luftstrøm fra bunn til bak med temperaturstyrte vifter; integrert modul for overvåking av chassis (CMM)

Bredt vekselstrøminngang med hovedbryter på baksiden, strømknapp på bakre (øvre) bakre panel eksterne 10 MHz klokkeinnganger/utganger



PRODUKTEGENSKAPER

Produkttype: System

Antall spor: 18

Type: Skrivebord

Bakplantype: PXI Express, 4-koblingskonfigurasjon

Dataoverføring: PCIe Gen3

Strøm per spor: 50W

Inngangsspenning AC: 100 – 240V

Luftstrømretning: Bunn til bakside

Rackhøyde: 4U

Strømforsyningstype: Åpen ramme

Strømforsyning inkludert: Ja

Bakre i/U: Nei

Samsvarer med: PXISA PXI-5 R1.1

Antall tidsspor for PXI Express: 1

Dybde: 355mm

Nettovekt: 14kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

System i samsvar med IEC 60297-3-101, -102, -103; IEEE 1101,1, 1101,10/11); bakplan, er i samsvar med picmg rev. 3,0 og PXI-5

Modifiserte systemer tilgjengelig på forespørsel

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE