

# nVent ERIFLEX Flexibar Zaawansowane, Miedź ocynowana



After extensive research, nVent ERIFLEX is proud to establish a new gold standard in terms of insulation for flexible busbar called nVent ERIFLEX Flexibar Advanced. The new product is low smoke, halogen-free and flame retardant all while maintaining the level of flexibility and reliability that our partners have come to expect from nVent ERIFLEX Flexibar.

Compared to standard PVC insulation, nVent ERIFLEX Flexibar Advanced does not generate corrosive gases and produces a relatively low smoke opacity in accordance with ISO 5659-2. The low smoke characteristic improves the visibility conditions for people to be able to easily locate the emergency exit and also allows rescue workers to assess an emergency situation more clearly. nVent ERIFLEX Flexibar Advanced means greater safety for individuals, less damage for your electrical equipment and less environmental impact.

The halogen-free feature enables a reduction in the quantity of toxic smoke. nVent ERIFLEX Flexibar Advanced does not contain any halogens, according to IEC 60754-1, minimizing toxicity and making it the ideal product for use in enclosed spaces such as data centers, rail and other spaces where people are welcome such as hospitals and schools. This also facilitates the use of nVent ERIFLEX Flexibar Advanced in specific applications such as submarines, switchboards and other enclosed environments that require a low emissions solution.

In addition to being halogen-free, nVent ERIFLEX Flexibar Advanced is also compliant with the UL 94-V0 testing standard. The flame retardant portion of the test illustrates the self-extinguish feature. This superior feature of nVent ERIFLEX Flexibar Advanced is also shown by the Limiting Oxygen Index (LOI) at 30%. In case of fire, ERIFLEX Flexibar Advanced generates a limited quantity of smoke that is less damaging to your electrical equipment.

## FUNKCJE

Zgodność z normą RoHS

Thin layers of tinned electrolytic copper formed into a stack

Full range from 19.5 mm<sup>2</sup> up to 1200 mm<sup>2</sup> and 125 A to 2800 A

Insulated by high-resistance, halogen free, flame retardant and low smoke material with less than 20% contact with conductor for high flexibility

Easily bent, folded, and twisted, improving assembly flexibility, shortening connections, and decreasing footprint

Dramatically smaller and more flexible than comparable cable based on ampacity

Better power density than cable with lower skin effect ratio

Connections made by punching and bolting directly through the copper laminates or clamping onto the end of the nVent ERIFLEX Flexibar

No lugs needed, reducing installation time and improving resistance to vibration

Weight savings and material savings compared to wire alternatives

Reduces total installation cost

Traceability codes and designation part numbers printed on insulation

Conforms to NF EN 45545 obtaining an HL3 classification for chapters R22 and R23

100% production dielectric tested

Tinned copper allows for copper or aluminum conductor connections

On request, can be manufactured with other colors (typically with Orange sleeve for battery connection)

Compliant to ISO 6469-1 (Electrically propelled road vehicles - Part 1: Rechargeable energy storage system) - Section 6.2.2 Vibrations

UL® 758 Appliance Wiring Material, Model Style 11992

|                                                   |                                                                                     |
|---------------------------------------------------|-------------------------------------------------------------------------------------|
| <b>Grubość izolacji:</b>                          | 1.8 mm                                                                              |
| <b>Wytrzymałość dielektryczna:</b>                | 20                                                                                  |
| <b>Wydłużenie izolacji:</b>                       | 500 %                                                                               |
| <b>Maks. napięcie robocze, UL/CSA/IEC:</b>        | 1000V;1500V                                                                         |
| <b>Maks. napięcie robocze, EN 50264-3-1:</b>      | 6000V                                                                               |
| <b>Temperatura robocza:</b>                       | -50 to 115 °C                                                                       |
| <b>Materiał:</b>                                  | Miedź;Elastomer termoplastyczny                                                     |
| <b>Zgodność z:</b>                                | IEC® 60695-2-11 (próba rozżarzonego drutu 960°C);IEC® 61439.1;IEC® 61439.1 klasa II |
| <b>Bez zawartości halogenów:</b>                  | UL® 2885;IEC® 60754-1;IEC® 62821-1                                                  |
| <b>Dymienie, ocena toksyczności i kwasowości:</b> | IEC® 60754-2                                                                        |
| <b>Niska wartość emisji dymu:</b>                 | IEC® 61034-2;ISO 5659-2;UL® 2885                                                    |
| <b>Wykończenie:</b>                               | Cynowany                                                                            |
| <b>Odporność na promieniowanie UV:</b>            | UL® 854;UL® 2556                                                                    |
| <b>Szczegóły dotyczące certyfikacji:</b>          | UL® 67;UL® 758 styl 11992                                                           |
| <b>Klasyfikacja palności:</b>                     | UL® 94V-0                                                                           |



## SPECYFIKACJE

Table 1/4

| Numer katalogowy | Numer artykułu | Prąd znamionowy typowego zastosowania, IEC | Długość (L) | ΔT 30 K | ΔT 40 K | ΔT 50 K |
|------------------|----------------|--------------------------------------------|-------------|---------|---------|---------|
| FADV2MTC8X6      | 534000         | 125 A                                      | 2000mm      | 131A    | 143A    | 166A    |
| FADV2MTC6X13     | 534005         | 250 A                                      | 2000mm      | 188A    | 226A    | 253A    |
| FADV2MTC3X13     | 534004         | 125 A                                      | 2000mm      | 128A    | 150A    | 167A    |
| FADV2MTC10X15-5  | 534009         | 400 A                                      | 2000mm      | 387A    | 407A    | 455A    |
| FADV2MTC3X9      | 534001         | 125 A                                      | 2000mm      | 126A    | 120A    | 134A    |
| FADV2MTC6X15-5   | 534008         | 400 A                                      | 2000mm      | 282A    | 360A    | 402A    |
| FADV2MTC2X15-5   | 534006         | 125 A                                      | 2000mm      | 152A    | 191A    | 212A    |

| Numer katalogowy | Numer artykułu | Prąd znamionowy typowego zastosowania, IEC | Długość (L) | ΔT 30K | ΔT 40K | ΔT 50K |
|------------------|----------------|--------------------------------------------|-------------|--------|--------|--------|
| FADV2MTC4X15-5   | 534007         | 250 A                                      | 2000mm      | 223A   | 286A   | 320A   |
| FADV2MTC6X9      | 534002         | 125 A                                      | 2000mm      | 192A   | 220A   | 245A   |
| FADV2MTC9X9      | 534003         | 250 A                                      | 2000mm      | 251A   | 237A   | 265A   |
| FADV3MTC3X50X1   | 534137         | 500 A                                      | 3000mm      | 562A   | 530A   | 592A   |
| FADV3MTC3X20X1   | 534111         | 250 A                                      | 3000mm      | 263A   | 323A   | 360A   |
| FADV3MTC4X32X1   | 534125         | 500 A                                      | 3000mm      | 449A   | 490A   | 548A   |
| FADV3MTC6X32X1   | 534127         | 630 A                                      | 3000mm      | 561A   | 640A   | 715A   |
| FADV3MTC3X40X1   | 534131         | 500 A                                      | 3000mm      | 464A   | 466A   | 522A   |
| FADV3MTC4X50X1   | 534138         | 630 A                                      | 3000mm      | 651A   | 650A   | 727A   |
| FADV3MTC2X24X1   | 534116         | 250 A                                      | 3000mm      | 244A   | 340A   | 380A   |
| FADV2MTC8X50X1   | 534041         | 1000 A                                     | 2000mm      | 927A   | 1050A  | 1175A  |
| FADV2MTC8X32X1   | 534028         | 800 A                                      | 2000mm      | 657A   | 770A   | 860A   |
| FADV2MTC8X63X1   | 534047         | 1250 A                                     | 2000mm      | 1108A  | 1245A  | 1395A  |

Table 2/4

| Numer katalogowy | Numer artykułu | Prąd znamionowy typowego zastosowania, IEC | Długość (L) | ΔT 30 K | ΔT 40 K | ΔT 50 K |
|------------------|----------------|--------------------------------------------|-------------|---------|---------|---------|
| FADV3MTC6X24X1   | 534120         | 500 A                                      | 3000mm      | 448A    | 506A    | 566A    |
| FADV3MTC5X20X1   | 534113         | 400 A                                      | 3000mm      | 351A    | 376A    | 420A    |
| FADV3MTC3X32X1   | 534124         | 400 A                                      | 3000mm      | 385A    | 430A    | 480A    |
| FADV3MTC2X32X1   | 534123         | 400 A                                      | 3000mm      | 311A    | 363A    | 406A    |
| FADV3MTC6X20X1   | 534114         | 400 A                                      | 3000mm      | 390A    | 413A    | 462A    |
| FADV3MTC5X24X1   | 534119         | 500 A                                      | 3000mm      | 403A    | 460A    | 514A    |
| FADV3MTC3X24X1   | 534117         | 400 A                                      | 3000mm      | 304A    | 370A    | 413A    |
| FADV2MTC8X80X1   | 534052         | 1600 A                                     | 2000mm      | 1341A   | 1430A   | 1600A   |
| FADV3MTC5X50X1   | 534139         | 800 A                                      | 3000mm      | 730A    | 830A    | 930A    |
| FADV3MTC5X32X1   | 534126         | 630 A                                      | 3000mm      | 507A    | 573A    | 640A    |
| FADV2MTC8X40X1   | 534035         | 1000 A                                     | 2000mm      | 786A    | 930A    | 1040A   |
| FADV3MTC8X32X1   | 534128         | 800 A                                      | 3000mm      | 657A    | 770A    | 860A    |
| FADV3MTC4X24X1   | 534118         | 400 A                                      | 3000mm      | 356A    | 416A    | 465A    |
| FADV3MTC4X20X1   | 534112         | 400 A                                      | 3000mm      | 308A    | 360A    | 402A    |
| FADV3MTC2X20X1   | 534110         | 250 A                                      | 3000mm      | 211A    | 246A    | 275A    |
| FADV3MTC6X40X1   | 534134         | 800 A                                      | 3000mm      | 669A    | 770A    | 860A    |
| FADV2MTC3X20X1   | 534011         | 250 A                                      | 2000mm      | 263A    | 323A    | 360A    |
| FADV2MTC4X24X1   | 534018         | 400 A                                      | 2000mm      | 356A    | 416A    | 465A    |

| Numer katalogowy | Numer artykułu | Prąd znamionowy typowego zastosowania, IEC | Długość (L) | ΔT 30K | ΔT 40K | ΔT 50K |
|------------------|----------------|--------------------------------------------|-------------|--------|--------|--------|
| FADV2MTC12X100   | 534059         | 1600 A                                     | 2000mm      | 1920A  | 1890A  | 2115A  |
| FADV2MTC10X50X1  | 534042         | 1250 A                                     | 2000mm      | 1040A  | 1245A  | 1395A  |

Table 3/4

| Numer katalogowy | Numer artykułu | Prąd znamionowy typowego zastosowania, IEC | Długość (L) | ΔT 30 K | ΔT 40 K | ΔT 50 K |
|------------------|----------------|--------------------------------------------|-------------|---------|---------|---------|
| FADV2MTC5X80X1   | 534050         | 1000 A                                     | 2000mm      | 1077A   | 1050A   | 1175A   |
| FADV2MTC6X63X1   | 534046         | 1000 A                                     | 2000mm      | 966A    | 1085A   | 1215A   |
| FADV2MTC4X40X1   | 534032         | 500 A                                      | 2000mm      | 541A    | 550A    | 615A    |
| FADV2MTC5X63X1   | 534045         | 1000 A                                     | 2000mm      | 883A    | 920A    | 1030A   |
| FADV2MTC2X40X1   | 534030         | 400 A                                      | 2000mm      | 376A    | 406A    | 455A    |
| FADV2MTC4X50X1   | 534038         | 630 A                                      | 2000mm      | 651A    | 650A    | 727A    |
| FADV2MTC6X80X1   | 534051         | 1250 A                                     | 2000mm      | 1172A   | 1230A   | 1375A   |
| FADV2MTC10X100   | 534058         | 1600 A                                     | 2000mm      | 1765A   | 1775A   | 1985A   |
| FADV2MTC5X50X1   | 534039         | 800 A                                      | 2000mm      | 730A    | 830A    | 930A    |
| FADV2MTC4X63X1   | 534044         | 800 A                                      | 2000mm      | 792A    | 763A    | 855A    |
| FADV2MTC10X20X1  | 534015         | 630 A                                      | 2000mm      | 532A    | 576A    | 645A    |
| FADV2MTC6X50X1   | 534040         | 1000 A                                     | 2000mm      | 802A    | 925A    | 1035A   |
| FADV2MTC4X32X1   | 534025         | 500 A                                      | 2000mm      | 449A    | 490A    | 548A    |
| FADV2MTC6X100X1  | 534056         | 1250 A                                     | 2000mm      | 1414A   | 1393A   | 1550A   |
| FADV2MTC3X24X1   | 534017         | 400 A                                      | 2000mm      | 304A    | 370A    | 413A    |
| FADV2MTC6X40X1   | 534034         | 800 A                                      | 2000mm      | 669A    | 770A    | 860A    |
| FADV2MTC10X120   | 534060         | 1600 A                                     | 2000mm      | 2049A   | 2070A   | 2330A   |
| FADV2MTC4X20X1   | 534012         | 400 A                                      | 2000mm      | 308A    | 360A    | 402A    |
| FADV2MTC3X32X1   | 534024         | 400 A                                      | 2000mm      | 385A    | 430A    | 480A    |
| FADV2MTC10X63X1  | 534048         | 1600 A                                     | 2000mm      | 1232A   | 1435A   | 1600A   |

Table 4/4

| Numer katalogowy | Numer artykułu | Prąd znamionowy typowego zastosowania, IEC | Długość (L) | ΔT 30 K | ΔT 40 K | ΔT 50 K |
|------------------|----------------|--------------------------------------------|-------------|---------|---------|---------|
| FADV2MTC6X32X1   | 534027         | 630 A                                      | 2000mm      | 561A    | 640A    | 715A    |
| FADV2MTC10X80X1  | 534053         | 1600 A                                     | 2000mm      | 1484A   | 1585A   | 1775A   |
| FADV2MTC3X40X1   | 534031         | 500 A                                      | 2000mm      | 464A    | 466A    | 522A    |
| FADV2MTC6X24X1   | 534020         | 500 A                                      | 2000mm      | 448A    | 506A    | 566A    |
| FADV2MTC3X50X1   | 534037         | 500 A                                      | 2000mm      | 562A    | 530A    | 592A    |
| FADV2MTC6X20X1   | 534014         | 400 A                                      | 2000mm      | 390A    | 413A    | 462A    |

| Numer katalogowy | Numer artykułu | Prąd znamionowy typowego zastosowania, IEC | Długość (L) | ΔT 30K | ΔT 40K | ΔT 50K |
|------------------|----------------|--------------------------------------------|-------------|--------|--------|--------|
| FADV2MTC5X40X1   | 534033         | 630 A                                      | 2000mm      | 608A   | 680A   | 760A   |
| FADV2MTC5X32X1   | 534026         | 630 A                                      | 2000mm      | 507A   | 573A   | 640A   |
| FADV2MTC2X24X1   | 534016         | 250 A                                      | 2000mm      | 244A   | 340A   | 380A   |
| FADV2MTC5X100X1  | 534055         | 1250 A                                     | 2000mm      | 1301A  | 1235A  | 1385A  |
| FADV2MTC8X100X1  | 534057         | 1600 A                                     | 2000mm      | 1598A  | 1625A  | 1815A  |
| FADV2MTC2X32X1   | 534023         | 400 A                                      | 2000mm      | 311A   | 363A   | 406A   |
| FADV2MTC5X20X1   | 534013         | 400 A                                      | 2000mm      | 351A   | 376A   | 420A   |
| FADV2MTC4X80X1   | 534049         | 1000 A                                     | 2000mm      | 970A   | 906A   | 1015A  |
| FADV2MTC5X24X1   | 534019         | 500 A                                      | 2000mm      | 403A   | 460A   | 514A   |
| FADV2MTC10X32X1  | 534029         | 1000 A                                     | 2000mm      | 745A   | 930A   | 1040A  |
| FADV2MTC8X24X1   | 534021         | 630 A                                      | 2000mm      | 531A   | 606A   | 678A   |
| FADV2MTC2X20X1   | 534010         | 250 A                                      | 2000mm      | 211A   | 246A   | 275A   |
| FADV2MTC10X40X1  | 534036         | 1000 A                                     | 2000mm      | 879A   | 1055A  | 1181A  |
| FADV2MTC10X24X1  | 534022         | 800 A                                      | 2000mm      | 606A   | 716A   | 800A   |

Table 1/4

| Numer katalogowy | Numer artykułu | ΔT 60 K | Warstwy przewodzące (N) | A.      | B.     | Przekrój            |
|------------------|----------------|---------|-------------------------|---------|--------|---------------------|
| FADV2MTC8X6      | 534000         | 182A    | 8                       | 6 mm    | 0.5 mm | 24mm <sup>2</sup>   |
| FADV2MTC6X13     | 534005         | 277A    | 6                       | 13 mm   | 0.5 mm | 39mm <sup>2</sup>   |
| FADV2MTC3X13     | 534004         | 184A    | 3                       | 13 mm   | 0.5 mm | 19.5mm <sup>2</sup> |
| FADV2MTC10X15-5  | 534009         | 498A    | 10                      | 15.5 mm | 0.8 mm | 124mm <sup>2</sup>  |
| FADV2MTC3X9      | 534001         | 147A    | 3                       | 9 mm    | 0.8 mm | 21.6mm <sup>2</sup> |
| FADV2MTC6X15-5   | 534008         | 440A    | 6                       | 15.5 mm | 0.8 mm | 74.4mm <sup>2</sup> |
| FADV2MTC2X15-5   | 534006         | 234A    | 2                       | 15.5 mm | 0.8 mm | 24.8mm <sup>2</sup> |
| FADV2MTC4X15-5   | 534007         | 350A    | 4                       | 15.5 mm | 0.8 mm | 49.6mm <sup>2</sup> |
| FADV2MTC6X9      | 534002         | 269A    | 6                       | 9 mm    | 0.8 mm | 43.2mm <sup>2</sup> |
| FADV2MTC9X9      | 534003         | 291A    | 9                       | 9 mm    | 0.8 mm | 64.8mm <sup>2</sup> |
| FADV3MTC3X50X1   | 534137         | 650A    | 3                       | 50 mm   | 1 mm   | 150mm <sup>2</sup>  |
| FADV3MTC3X20X1   | 534111         | 395A    | 3                       | 20 mm   | 1 mm   | 60mm <sup>2</sup>   |
| FADV3MTC4X32X1   | 534125         | 600A    | 4                       | 32 mm   | 1 mm   | 128mm <sup>2</sup>  |
| FADV3MTC6X32X1   | 534127         | 783A    | 6                       | 32 mm   | 1 mm   | 192mm <sup>2</sup>  |
| FADV3MTC3X40X1   | 534131         | 570A    | 3                       | 40 mm   | 1 mm   | 120mm <sup>2</sup>  |
| FADV3MTC4X50X1   | 534138         | 795A    | 4                       | 50 mm   | 1 mm   | 200mm <sup>2</sup>  |
| FADV3MTC2X24X1   | 534116         | 416A    | 2                       | 24 mm   | 1 mm   | 48mm <sup>2</sup>   |

| Numer katalogowy | Numer artykułu | $\Delta T$ 60 K | Warstwy przewodzące (N) | A.    | B.   | Przekrój           |
|------------------|----------------|-----------------|-------------------------|-------|------|--------------------|
| FADV2MTC8X50X1   | 534041         | 1290A           | 8                       | 50 mm | 1 mm | 400mm <sup>2</sup> |
| FADV2MTC8X32X1   | 534028         | 943A            | 8                       | 32 mm | 1 mm | 256mm <sup>2</sup> |
| FADV2MTC8X63X1   | 534047         | 1525A           | 8                       | 63 mm | 1 mm | 504mm <sup>2</sup> |

Table 2/4

| Numer katalogowy | Numer artykułu | $\Delta T$ 60 K | Warstwy przewodzące (N) | A.     | B.   | Przekrój            |
|------------------|----------------|-----------------|-------------------------|--------|------|---------------------|
| FADV3MTC6X24X1   | 534120         | 620A            | 6                       | 24 mm  | 1 mm | 144mm <sup>2</sup>  |
| FADV3MTC5X20X1   | 534113         | 460A            | 5                       | 20 mm  | 1 mm | 100mm <sup>2</sup>  |
| FADV3MTC3X32X1   | 534124         | 525A            | 3                       | 32 mm  | 1 mm | 96mm <sup>2</sup>   |
| FADV3MTC2X32X1   | 534123         | 445A            | 2                       | 32 mm  | 1 mm | 64mm <sup>2</sup>   |
| FADV3MTC6X20X1   | 534114         | 506A            | 6                       | 20 mm  | 1 mm | 120mm <sup>2</sup>  |
| FADV3MTC5X24X1   | 534119         | 563A            | 5                       | 24 mm  | 1 mm | 120mm <sup>2</sup>  |
| FADV3MTC3X24X1   | 534117         | 453A            | 3                       | 24 mm  | 1 mm | 72mm <sup>2</sup>   |
| FADV2MTC8X80X1   | 534052         | 1755A           | 8                       | 80 mm  | 1 mm | 640mm <sup>2</sup>  |
| FADV3MTC5X50X1   | 534139         | 1016A           | 5                       | 50 mm  | 1 mm | 250mm <sup>2</sup>  |
| FADV3MTC5X32X1   | 534126         | 702A            | 5                       | 32 mm  | 1 mm | 160mm <sup>2</sup>  |
| FADV2MTC8X40X1   | 534035         | 1140A           | 8                       | 40 mm  | 1 mm | 320mm <sup>2</sup>  |
| FADV3MTC8X32X1   | 534128         | 943A            | 8                       | 32 mm  | 1 mm | 256mm <sup>2</sup>  |
| FADV3MTC4X24X1   | 534118         | 510A            | 4                       | 24 mm  | 1 mm | 96mm <sup>2</sup>   |
| FADV3MTC4X20X1   | 534112         | 440A            | 4                       | 20 mm  | 1 mm | 80mm <sup>2</sup>   |
| FADV3MTC2X20X1   | 534110         | 300A            | 2                       | 20 mm  | 1 mm | 40mm <sup>2</sup>   |
| FADV3MTC6X40X1   | 534134         | 943A            | 6                       | 40 mm  | 1 mm | 240mm <sup>2</sup>  |
| FADV2MTC3X20X1   | 534011         | 395A            | 3                       | 20 mm  | 1 mm | 60mm <sup>2</sup>   |
| FADV2MTC4X24X1   | 534018         | 510A            | 4                       | 24 mm  | 1 mm | 96mm <sup>2</sup>   |
| FADV2MTC12X100   | 534059         | 2315A           | 12                      | 100 mm | 1 mm | 1200mm <sup>2</sup> |
| FADV2MTC10X50X1  | 534042         | 1525A           | 10                      | 50 mm  | 1 mm | 500mm <sup>2</sup>  |

Table 3/4

| Numer katalogowy | Numer artykułu | $\Delta T$ 60 K | Warstwy przewodzące (N) | A.    | B.   | Przekrój           |
|------------------|----------------|-----------------|-------------------------|-------|------|--------------------|
| FADV2MTC5X80X1   | 534050         | 1285A           | 5                       | 80 mm | 1 mm | 400mm <sup>2</sup> |
| FADV2MTC6X63X1   | 534046         | 1330A           | 6                       | 63 mm | 1 mm | 378mm <sup>2</sup> |
| FADV2MTC4X40X1   | 534032         | 673A            | 4                       | 40 mm | 1 mm | 160mm <sup>2</sup> |
| FADV2MTC5X63X1   | 534045         | 1125A           | 5                       | 63 mm | 1 mm | 315mm <sup>2</sup> |
| FADV2MTC2X40X1   | 534030         | 500A            | 2                       | 40 mm | 1 mm | 80mm <sup>2</sup>  |
| FADV2MTC4X50X1   | 534038         | 795A            | 4                       | 50 mm | 1 mm | 200mm <sup>2</sup> |

| Numer katalogowy | Numer artykułu | ΔT 60 K | Warstwy przewodzące (N) | A.     | B.   | Przekrój            |
|------------------|----------------|---------|-------------------------|--------|------|---------------------|
| FADV2MTC6X80X1   | 534051         | 1505A   | 6                       | 80 mm  | 1 mm | 480mm <sup>2</sup>  |
| FADV2MTC10X100   | 534058         | 2170A   | 10                      | 100 mm | 1 mm | 1000mm <sup>2</sup> |
| FADV2MTC5X50X1   | 534039         | 1016A   | 5                       | 50 mm  | 1 mm | 250mm <sup>2</sup>  |
| FADV2MTC4X63X1   | 534044         | 935A    | 4                       | 63 mm  | 1 mm | 252mm <sup>2</sup>  |
| FADV2MTC10X20X1  | 534015         | 706A    | 10                      | 20 mm  | 1 mm | 200mm <sup>2</sup>  |
| FADV2MTC6X50X1   | 534040         | 1135A   | 6                       | 50 mm  | 1 mm | 300mm <sup>2</sup>  |
| FADV2MTC4X32X1   | 534025         | 600A    | 4                       | 32 mm  | 1 mm | 128mm <sup>2</sup>  |
| FADV2MTC6X100X1  | 534056         | 1705A   | 6                       | 100 mm | 1 mm | 600mm <sup>2</sup>  |
| FADV2MTC3X24X1   | 534017         | 453A    | 3                       | 24 mm  | 1 mm | 72mm <sup>2</sup>   |
| FADV2MTC6X40X1   | 534034         | 943A    | 6                       | 40 mm  | 1 mm | 240mm <sup>2</sup>  |
| FADV2MTC10X120   | 534060         | 2550A   | 10                      | 120 mm | 1 mm | 1200mm <sup>2</sup> |
| FADV2MTC4X20X1   | 534012         | 440A    | 4                       | 20 mm  | 1 mm | 80mm <sup>2</sup>   |
| FADV2MTC3X32X1   | 534024         | 525A    | 3                       | 32 mm  | 1 mm | 96mm <sup>2</sup>   |
| FADV2MTC10X63X1  | 534048         | 1755A   | 10                      | 63 mm  | 1 mm | 630mm <sup>2</sup>  |

Table 4/4

| Numer katalogowy | Numer artykułu | ΔT 60 K | Warstwy przewodzące (N) | A.     | B.   | Przekrój           |
|------------------|----------------|---------|-------------------------|--------|------|--------------------|
| FADV2MTC6X32X1   | 534027         | 783A    | 6                       | 32 mm  | 1 mm | 192mm <sup>2</sup> |
| FADV2MTC10X80X1  | 534053         | 1945A   | 10                      | 80 mm  | 1 mm | 800mm <sup>2</sup> |
| FADV2MTC3X40X1   | 534031         | 570A    | 3                       | 40 mm  | 1 mm | 120mm <sup>2</sup> |
| FADV2MTC6X24X1   | 534020         | 620A    | 6                       | 24 mm  | 1 mm | 144mm <sup>2</sup> |
| FADV2MTC3X50X1   | 534037         | 650A    | 3                       | 50 mm  | 1 mm | 150mm <sup>2</sup> |
| FADV2MTC6X20X1   | 534014         | 506A    | 6                       | 20 mm  | 1 mm | 120mm <sup>2</sup> |
| FADV2MTC5X40X1   | 534033         | 832A    | 5                       | 40 mm  | 1 mm | 200mm <sup>2</sup> |
| FADV2MTC5X32X1   | 534026         | 702A    | 5                       | 32 mm  | 1 mm | 160mm <sup>2</sup> |
| FADV2MTC2X24X1   | 534016         | 416A    | 2                       | 24 mm  | 1 mm | 48mm <sup>2</sup>  |
| FADV2MTC5X100X1  | 534055         | 1515A   | 5                       | 100 mm | 1 mm | 500mm <sup>2</sup> |
| FADV2MTC8X100X1  | 534057         | 1990A   | 8                       | 100 mm | 1 mm | 800mm <sup>2</sup> |
| FADV2MTC2X32X1   | 534023         | 445A    | 2                       | 32 mm  | 1 mm | 64mm <sup>2</sup>  |
| FADV2MTC5X20X1   | 534013         | 460A    | 5                       | 20 mm  | 1 mm | 100mm <sup>2</sup> |
| FADV2MTC4X80X1   | 534049         | 1110A   | 4                       | 80 mm  | 1 mm | 320mm <sup>2</sup> |
| FADV2MTC5X24X1   | 534019         | 563A    | 5                       | 24 mm  | 1 mm | 120mm <sup>2</sup> |
| FADV2MTC10X32X1  | 534029         | 1140A   | 10                      | 32 mm  | 1 mm | 320mm <sup>2</sup> |
| FADV2MTC8X24X1   | 534021         | 743A    | 8                       | 24 mm  | 1 mm | 192mm <sup>2</sup> |
| FADV2MTC2X20X1   | 534010         | 300A    | 2                       | 20 mm  | 1 mm | 40mm <sup>2</sup>  |
| FADV2MTC10X40X1  | 534036         | 1295A   | 10                      | 40 mm  | 1 mm | 400mm <sup>2</sup> |

| Numer katalogowy | Numer artykułu | $\Delta T$ 60 K | Warstwy przewodzące (N) | A.    | B.   | Przekrój           |
|------------------|----------------|-----------------|-------------------------|-------|------|--------------------|
| FADV2MTC10X24X1  | 534022         | 877A            | 10                      | 24 mm | 1 mm | 240mm <sup>2</sup> |

Table 1/4

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV2MTC8X6      | 534000         | 1.72                          | 2.25                          | cUR, Bureau Veritas, 02859/H0 BV, ABS, UR, CE, ERIFLEX FLEXADV, CSA, RoHS |
| FADV2MTC6X13     | 534005         | 1.72                          | 2.25                          | UR, RoHS, CSA, Bureau Veritas, 02859/H0 BV, cUR, ABS, CE, ERIFLEX FLEXADV |
| FADV2MTC3X13     | 534004         | 1.72                          | 2.25                          | CSA, RoHS, UR, CE, ERIFLEX FLEXADV, cUR, ABS, Bureau Veritas, 02859/H0 BV |
| FADV2MTC10X15-5  | 534009         | 1.72                          | 2.25                          | UR, CSA, RoHS, Bureau Veritas, 02859/H0 BV, ABS, CE, ERIFLEX FLEXADV, cUR |
| FADV2MTC3X9      | 534001         | 1.72                          | 2.25                          | RoHS, UR, CSA, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR, ABS |
| FADV2MTC6X15-5   | 534008         | 1.72                          | 2.25                          | ABS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, UR, cUR, CSA, RoHS |
| FADV2MTC2X15-5   | 534006         | 1.72                          | 2.25                          | UR, ABS, CE, ERIFLEX FLEXADV, cUR, Bureau Veritas, 02859/H0 BV, CSA, RoHS |
| FADV2MTC4X15-5   | 534007         | 1.72                          | 2.25                          | cUR, ABS, UR, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, RoHS, CSA |
| FADV2MTC6X9      | 534002         | 1.72                          | 2.25                          | Bureau Veritas, 02859/H0 BV, ABS, cUR, UR, CE, ERIFLEX FLEXADV, RoHS, CSA |
| FADV2MTC9X9      | 534003         | 1.72                          | 2.25                          | CSA, RoHS, UR, cUR, ABS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV |
| FADV3MTC3X50X1   | 534137         | 1.72                          | 2.25                          | CSA, RoHS, UR, CE, ERIFLEX FLEXADV, ABS, Bureau Veritas, 02859/H0 BV, cUR |
| FADV3MTC3X20X1   | 534111         | 1.72                          | 2.25                          | CSA, RoHS, UR, ABS, cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV |
| FADV3MTC4X32X1   | 534125         | 1.72                          | 2.25                          | Bureau Veritas, 02859/H0 BV, ABS, UR, cUR, CE, ERIFLEX FLEXADV, CSA, RoHS |
| FADV3MTC6X32X1   | 534127         | 1.72                          | 2.25                          | ABS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR, UR, CSA, RoHS |
| FADV3MTC3X40X1   | 534131         | 1.72                          | 2.25                          | ABS, Bureau Veritas, 02859/H0 BV, UR, CE, ERIFLEX FLEXADV, cUR, CSA, RoHS |
| FADV3MTC4X50X1   | 534138         | 1.72                          | 2.25                          | RoHS, UR, CSA, CE, ERIFLEX FLEXADV, ABS, cUR, Bureau Veritas, 02859/H0 BV |
| FADV3MTC2X24X1   | 534116         | 1.72                          | 2.25                          | UR, RoHS, CSA, CE, ERIFLEX FLEXADV, cUR, Bureau Veritas, 02859/H0 BV, ABS |
| FADV2MTC8X50X1   | 534041         | 1.72                          | 2.25                          | CSA, UR, RoHS, CE, ERIFLEX FLEXADV, cUR, Bureau Veritas, 02859/H0 BV, ABS |

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV2MTC8X32X1   | 534028         | 1.72                          | 2.25                          | CSA, UR, RoHS, ABS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, cUR |
| FADV2MTC8X63X1   | 534047         | 1.65                          | 2.12                          | UR, CSA, RoHS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR, ABS |

Table 2/4

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV3MTC6X24X1   | 534120         | 1.72                          | 2.25                          | CSA, RoHS, UR, Bureau Veritas, 02859/H0 BV, ABS, cUR, CE, ERIFLEX FLEXADV |
| FADV3MTC5X20X1   | 534113         | 1.72                          | 2.25                          | cUR, ABS, UR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, CSA, RoHS |
| FADV3MTC3X32X1   | 534124         | 1.72                          | 2.25                          | UR, CSA, RoHS, ABS, cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV |
| FADV3MTC2X32X1   | 534123         | 1.72                          | 2.25                          | cUR, ABS, CE, ERIFLEX FLEXADV, UR, Bureau Veritas, 02859/H0 BV, RoHS, CSA |
| FADV3MTC6X20X1   | 534114         | 1.72                          | 2.25                          | CE, ERIFLEX FLEXADV, cUR, Bureau Veritas, 02859/H0 BV, UR, ABS, CSA, RoHS |
| FADV3MTC5X24X1   | 534119         | 1.72                          | 2.25                          | CSA, RoHS, UR, ABS, CE, ERIFLEX FLEXADV, cUR, Bureau Veritas, 02859/H0 BV |
| FADV3MTC3X24X1   | 534117         | 1.72                          | 2.25                          | UR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR, ABS, RoHS, CSA |
| FADV2MTC8X80X1   | 534052         | 1.65                          | 2.12                          | cUR, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, ABS, UR, CSA, RoHS |
| FADV3MTC5X50X1   | 534139         | 1.72                          | 2.25                          | UR, CSA, RoHS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR, ABS |
| FADV3MTC5X32X1   | 534126         | 1.72                          | 2.25                          | ABS, UR, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, cUR, RoHS, CSA |
| FADV2MTC8X40X1   | 534035         | 1.72                          | 2.25                          | cUR, ABS, Bureau Veritas, 02859/H0 BV, UR, CE, ERIFLEX FLEXADV, CSA, RoHS |
| FADV3MTC8X32X1   | 534128         | 1.72                          | 2.25                          | Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, cUR, ABS, UR, RoHS, CSA |
| FADV3MTC4X24X1   | 534118         | 1.72                          | 2.25                          | UR, CSA, RoHS, ABS, Bureau Veritas, 02859/H0 BV, cUR, CE, ERIFLEX FLEXADV |
| FADV3MTC4X20X1   | 534112         | 1.72                          | 2.25                          | UR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, ABS, cUR, CSA, RoHS |
| FADV3MTC2X20X1   | 534110         | 1.72                          | 2.25                          | cUR, UR, CE, ERIFLEX FLEXADV, ABS, Bureau Veritas, 02859/H0 BV, CSA, RoHS |
| FADV3MTC6X40X1   | 534134         | 1.72                          | 2.25                          | CSA, RoHS, UR, cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, ABS |

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV2MTC3X20X1   | 534011         | 1.72                          | 2.25                          | cUR, ABS, CE, ERIFLEX FLEXADV, UR, Bureau Veritas, 02859/H0 BV, CSA, RoHS |
| FADV2MTC4X24X1   | 534018         | 1.72                          | 2.25                          | Bureau Veritas, 02859/H0 BV, cUR, ABS, CE, ERIFLEX FLEXADV, UR, CSA, RoHS |
| FADV2MTC12X100   | 534059         | 1.6                           | 2.02                          | UR, RoHS, CSA, cUR, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, ABS |
| FADV2MTC10X50X1  | 534042         | 1.72                          | 2.25                          | UR, Bureau Veritas, 02859/H0 BV, ABS, cUR, CE, ERIFLEX FLEXADV, RoHS, CSA |

Table 3/4

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV2MTC5X80X1   | 534050         | 1.65                          | 2.12                          | CSA, RoHS, UR, Bureau Veritas, 02859/H0 BV, ABS, CE, ERIFLEX FLEXADV, cUR |
| FADV2MTC6X63X1   | 534046         | 1.65                          | 2.12                          | Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, ABS, UR, cUR, RoHS, CSA |
| FADV2MTC4X40X1   | 534032         | 1.72                          | 2.25                          | cUR, Bureau Veritas, 02859/H0 BV, ABS, UR, CE, ERIFLEX FLEXADV, RoHS, CSA |
| FADV2MTC5X63X1   | 534045         | 1.65                          | 2.12                          | ABS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR, UR, CSA, RoHS |
| FADV2MTC2X40X1   | 534030         | 1.72                          | 2.25                          | CE, ERIFLEX FLEXADV, cUR, ABS, Bureau Veritas, 02859/H0 BV, UR, CSA, RoHS |
| FADV2MTC4X50X1   | 534038         | 1.72                          | 2.25                          | CSA, UR, RoHS, cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, ABS |
| FADV2MTC6X80X1   | 534051         | 1.65                          | 2.12                          | CSA, RoHS, UR, ABS, cUR, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV |
| FADV2MTC10X100   | 534058         | 1.6                           | 2.02                          | RoHS, CSA, UR, cUR, ABS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV |
| FADV2MTC5X50X1   | 534039         | 1.72                          | 2.25                          | UR, RoHS, CSA, ABS, cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV |
| FADV2MTC4X63X1   | 534044         | 1.65                          | 2.12                          | ABS, CE, ERIFLEX FLEXADV, UR, Bureau Veritas, 02859/H0 BV, cUR, CSA, RoHS |
| FADV2MTC10X20X1  | 534015         | 1.72                          | 2.25                          | cUR, Bureau Veritas, 02859/H0 BV, UR, ABS, CE, ERIFLEX FLEXADV, CSA, RoHS |
| FADV2MTC6X50X1   | 534040         | 1.72                          | 2.25                          | CSA, UR, RoHS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, cUR, ABS |
| FADV2MTC4X32X1   | 534025         | 1.72                          | 2.25                          | CSA, UR, RoHS, cUR, Bureau Veritas, 02859/H0 BV, ABS, CE, ERIFLEX FLEXADV |
| FADV2MTC6X100X1  | 534056         | 1.6                           | 2.02                          | cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, ABS, UR, CSA, RoHS |

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV2MTC3X24X1   | 534017         | 1.72                          | 2.25                          | UR, RoHS, CSA, Bureau Veritas, 02859/H0 BV, ABS, cUR, CE, ERIFLEX FLEXADV |
| FADV2MTC6X40X1   | 534034         | 1.72                          | 2.25                          | UR, ABS, cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, RoHS, CSA |
| FADV2MTC10X120   | 534060         | 1.49                          | 1.95                          | CE, ERIFLEX FLEXADV, ABS, Bureau Veritas, 02859/H0 BV                     |
| FADV2MTC4X20X1   | 534012         | 1.72                          | 2.25                          | CSA, UR, RoHS, CE, ERIFLEX FLEXADV, ABS, cUR, Bureau Veritas, 02859/H0 BV |
| FADV2MTC3X32X1   | 534024         | 1.72                          | 2.25                          | UR, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, ABS, cUR, CSA, RoHS |
| FADV2MTC10X63X1  | 534048         | 1.65                          | 2.12                          | UR, CSA, RoHS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, ABS, cUR |

Table 4/4

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV2MTC6X32X1   | 534027         | 1.72                          | 2.25                          | CSA, UR, RoHS, ABS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, cUR |
| FADV2MTC10X80X1  | 534053         | 1.65                          | 2.12                          | cUR, ABS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, UR, CSA, RoHS |
| FADV2MTC3X40X1   | 534031         | 1.72                          | 2.25                          | UR, RoHS, CSA, ABS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR |
| FADV2MTC6X24X1   | 534020         | 1.72                          | 2.25                          | Bureau Veritas, 02859/H0 BV, UR, ABS, CE, ERIFLEX FLEXADV, cUR, RoHS, CSA |
| FADV2MTC3X50X1   | 534037         | 1.72                          | 2.25                          | Bureau Veritas, 02859/H0 BV, cUR, CE, ERIFLEX FLEXADV, ABS, UR, CSA, RoHS |
| FADV2MTC6X20X1   | 534014         | 1.72                          | 2.25                          | CSA, RoHS, UR, CE, ERIFLEX FLEXADV, ABS, cUR, Bureau Veritas, 02859/H0 BV |
| FADV2MTC5X40X1   | 534033         | 1.72                          | 2.25                          | ABS, cUR, UR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, RoHS, CSA |
| FADV2MTC5X32X1   | 534026         | 1.72                          | 2.25                          | CSA, RoHS, UR, Bureau Veritas, 02859/H0 BV, cUR, ABS, CE, ERIFLEX FLEXADV |
| FADV2MTC2X24X1   | 534016         | 1.72                          | 2.25                          | cUR, Bureau Veritas, 02859/H0 BV, ABS, CE, ERIFLEX FLEXADV, UR, CSA, RoHS |
| FADV2MTC5X100X1  | 534055         | 1.6                           | 2.02                          | UR, CE, ERIFLEX FLEXADV, cUR, ABS, Bureau Veritas, 02859/H0 BV, CSA, RoHS |
| FADV2MTC8X100X1  | 534057         | 1.6                           | 2.02                          | RoHS, CSA, UR, Bureau Veritas, 02859/H0 BV, ABS, cUR, CE, ERIFLEX FLEXADV |
| FADV2MTC2X32X1   | 534023         | 1.72                          | 2.25                          | UR, CSA, RoHS, cUR, Bureau Veritas, 02859/H0 BV, ABS, CE, ERIFLEX FLEXADV |

| Numer katalogowy | Numer artykułu | Współczynnik korekcyjny 2 bar | Współczynnik korekcyjny 3 bar | Certyfikaty                                                               |
|------------------|----------------|-------------------------------|-------------------------------|---------------------------------------------------------------------------|
| FADV2MTC5X20X1   | 534013         | 1.72                          | 2.25                          | RoHS, CSA, UR, cUR, ABS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV |
| FADV2MTC4X80X1   | 534049         | 1.65                          | 2.12                          | UR, CSA, RoHS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, cUR, ABS |
| FADV2MTC5X24X1   | 534019         | 1.72                          | 2.25                          | UR, cUR, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, ABS, CSA, RoHS |
| FADV2MTC10X32X1  | 534029         | 1.72                          | 2.25                          | ABS, CE, ERIFLEX FLEXADV, UR, cUR, Bureau Veritas, 02859/H0 BV, CSA, RoHS |
| FADV2MTC8X24X1   | 534021         | 1.72                          | 2.25                          | cUR, UR, ABS, Bureau Veritas, 02859/H0 BV, CE, ERIFLEX FLEXADV, CSA, RoHS |
| FADV2MTC2X20X1   | 534010         | 1.72                          | 2.25                          | CSA, RoHS, UR, CE, ERIFLEX FLEXADV, cUR, ABS, Bureau Veritas, 02859/H0 BV |
| FADV2MTC10X40X1  | 534036         | 1.72                          | 2.25                          | CSA, UR, RoHS, CE, ERIFLEX FLEXADV, Bureau Veritas, 02859/H0 BV, cUR, ABS |
| FADV2MTC10X24X1  | 534022         | 1.72                          | 2.25                          | CSA, UR, RoHS, CE, ERIFLEX FLEXADV, cUR, Bureau Veritas, 02859/H0 BV, ABS |


## DODATKOWE INFORMACJE O PRODUKCIE

ADMISSIBLE CURRENTS: This table indicates the temperature rise produced by chosen current in the given section. This calculation does not take into account the heat dissipation from the switch gear.

$\Delta T$  = Temperature of conductors – Internal temperature of panel.

Refer to technical documentation for additional ampacity ratings.

## SCHEMATY



## OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie [www.nvent.com](http://www.nvent.com) oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę

gwarancji.

#### **Ameryka Północna**

+1.800.753.9221

Opcja 1 – obsługa klienta

Opcja 2 – wsparcie

techniczne

#### **Europa**

Niderlandy:

+31 800-0200135

Francja:

+33 800 901 793

#### **Europa**

Niemcy:

800 1890272

Inne kraje:

+31 13 5835404

#### **APAC**

Szanghaj:

+ 86 21 2412 1618/19

Sydney:

+61 2 975 185 00



Marki w naszej ofercie:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

©2026 nVent. Wszystkie znaki i logo nVent są własnością firmy nVent Services GmbH albo jej spółek zależnych lub są licencjonowane. Wszystkie pozostałe znaki towarowe są własnością odpowiednich właścicieli. Firma nVent zastrzega sobie prawo do zmiany specyfikacji bez powiadomienia.

Ten dokument jest generowany przez system.