

Systemy oczyszczania i ciśnieniowego



Purge and Pressurization is a protection method used with Type 4, 4X and 12 (IP54 recommended minimum) enclosures. The enclosure is initially purged to remove any internal explosive gases or dust. Once this is accomplished, the enclosure is pressurized with a protective air or inert gas supply. This provides a positive internal enclosure pressure which keeps any external explosive gases or dust from entering the enclosure. The two methods of purge and pressurization offered are Leak Compensation and Continuous Flow.

Leak Compensation maintains positive pressure by compensating for losses. System consists of Control Unit and Relief Valve. Certification Type Y and Z models: • Flush (internal) or external mount models • Local visual alarm indicator and dry contact output for remote alarm • Typically recommended for enclosures with volume of 60 Ft³ or less. Certification Type X Model: • Provides power disconnect when pressurization is lost or not attained • Provides automatic purge process • External mount • Local visual alarm indicator and dry contact output for remote alarm • Typically recommended for enclosures with volume of 60 Ft³ or less.

Continuous Flow provides positive pressure via continuous protective air flow through the enclosure. System consists of Control Unit, Calibrated Outlet Orifice and Relief Valve. Certification Type Y and Z Models: • Flush (internal) or external mount models • Local visual alarm indicator and dry contact output for remote alarm • Typically recommended for enclosures with volume of 17 Ft³ or less

NORMY BRANŻOWE

Type X

Ex [px] Ex [p]

IECEX SIR.0019X [Gb, Db]

Europe, ATEX Category 2 GD

Cert no Sira 14ATEX1045X

USA/Canada NFPA496 CI I Div 1 Groups A, B, C & D

UL E466718

Type Y

Ex [py] Ex [p]

IECEX SIR.0019X [Gb, Db]

Europe, ATEX Category 2 GD

Cert no Sira 14ATEX1045X

North America CI I Div 1 Groups A, B, C & D

For protecting CI I Div 2 equipment

UL E466718

Type Z

Ex [pz] Ex [p]

IECEX SIR.0019X [Gc, Dc]

Europe, ATEX Category 3 GD

Cert no Sira 14ATEX1045X

North America CI I Div 2 Groups A, B, C & D

UL E466718

FUNKCJE

All exterior components are 316 stainless steel or corrosion-resistant composite

Space-saving flush or exterior mounted models available

Local visual indicators provide system status

Leak compensation models are equipped with rapid purge valve and visual purge status indicator

All models utilize dry, clean inert gas supply of 60 PSI (4 bar) to 115 PSI (8 bar)

Ambient operating temperature -4°F (-20°C) to 131°F (55°C)

Type X models provide automatic purge cycle and 4PNO/20A/440VAC power contactor with 115 VAC or 230 VAC coil

Materiał: Stal nierdzewna 316L

Wykończenie: Powierzchnia szczotkowana

SPECYFIKACJE

Numer katalogowy	Grubość	Typ operacji	Montaż	Szczegóły dotyczące certyfikacji
PCFB1YZ	3.18mm	Przepływ ciągły	Na zewnątrz	Typ Y, Typ Z.
PCFF1YZ	3.18mm	Przepływ ciągły	Przepłukiwanie	Typ Y, Typ Z.
PCFSKIT				
PLCB1YZ	3.18mm	Kompensacja wycieków	Na zewnątrz	
PLCF1YZ	3.18mm	Kompensacja wycieków	Przepłukiwanie	Typ Y, Typ Z.
PLCS1X1	3.18mm	Kompensacja wycieków	Na zewnątrz	Typ X.
PLCS1X2	3.18mm	Kompensacja wycieków	Na zewnątrz	Typ X.
PLCSKIT				

DODATKOWE INFORMACJE O PRODUKCIE

For all IEC and ATEC applications, the final or complete integrated assembly must be submitted to a notified body for certification.

See Specification Sheet for Purge and Pressurization Systems and Certifications table.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



©2026 nVent. Wszystkie znaki i logo nVent są własnością firmy nVent Services GmbH albo jej spółek zależnych lub są licencjonowane. Wszystkie pozostałe znaki towarowe są własnością odpowiednich właścicieli. Firma nVent zastrzega sobie prawo do zmiany specyfikacji bez powiadomienia.

Ten dokument jest generowany przez system.