

PXI System With ATX PSU, 4 U, 8 slots, 44 HP

NÚMERO DE CATÁLOGO

14579-008

Chasis de escritorio PXI con jaula de tarjeta vertical para ocho placas de 3 U y fuente de alimentación incorporada.

CARACTERÍSTICAS

Sistema de acuerdo con IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11); Backplane, cumple con PICMG rev. 3.0 y PXI 2.0

Chasis de escritorio PXI, 4 U, 44 HP con jaula de tarjeta vertical. Formato de la placa frontal: 3U, 160 mm

Backplane, 8 ranuras, 3 HE, 64 bit, ranura del sistema izquierda

Disipación de calor con flujo de aire de fondo hacia atrás

Fuente de alimentación ATX 400 W, entrada de CA de amplio rango con interruptor de alimentación en la parte trasera

Backplane con cambio de reloj interno / externo



ATRIBUTOS DEL PRODUCTO

Tipo de producto: Sistema

Número de ranuras: 8

Tipo: Escritorio

Tipo de panel posterior: 3 U CompactPCI con PXIbus

Transferencia de datos: 64-bit PCI Bus

Potencia por ranura: 30W

Tensión de entrada de CA: 100 – 240V

Dirección del flujo de aire: De abajo a la parte trasera

Altura del rack: 4U

Tipo de fuente de alimentación: Marco abierto

Fuente de alimentación incluida: Sí

E/S posterior: No

De conformidad con: PXISA PXI-1 R2.0

Fondo: 355mm

Peso neto: 9.6kg

Cantidad del paquete: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Sistemas modificados disponibles bajo petición.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE