


# Tornillo de cabeza cilíndrica, Torx 8, autofreno, M2,5 x 9,3 mm, acero cincado; 100 piezas

## NÚMERO DE CATÁLOGO

**21500-039**



Tornillos torx de cabeza de cacerola con diferentes roscas métricas y longitudes. Con características opcionales como la función de puesta a tierra GND o el hilo de autosujeción.

Tornillo Panhead, Torx, St, zincado, M2.5 x 6 (rosca parcialmente recubierta para evitar que el tornillo se afloje por sí solo debido a las vibraciones)

## CARACTERÍSTICAS

Tornillo de cabeza de cacerola con torx, auto-bloqueo

The star-shaped head prevents cam-out



## ATRIBUTOS DEL PRODUCTO

Longitud: 9.3mm

Acabado: Zinc plateado

Cantidad del paquete: 100

Tamaño de rosca: M2.5

Material: Acero

Tipo de producto: Tornillo

Tipo: Tornillo Panhead

Compatible con: Paneles frontales; Rieles horizontales, tipo H; Rieles horizontales, tipo R

Drive Type Main: Torx 8

Head Shape: Panhead

Peso bruto: 0.037kg

Longitud de rosca: 9.3mm

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DETALLES ADICIONALES DEL PRODUCTO

Par máx. 0,2 Nm.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

