

nVent CADDY Speed Link SLK with Loop



CARACTERÍSTICAS

Complete system includes wire, locking device and pre-assembled loop end fitting

Easy and flexible solution attaches to building structures

Wire rope wraps around structure and through loop for quick installation

Ideal for attaching to purlins, beams and other structural members

Works well in tight or confined spaces

Loop attaches directly to pipe, ductwork or other hanging assemblies

Material: Aço; Polypropylene; Liga de zinco
Acabamento: Electrogalvanized
Static Load Safety Factor: 5:1
Em conformidade com: SMACNA HVAC-DCS



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Wire Rope Diameter	Wire Rope Length	Length (L)	Altura (H)	Largura (W)
SLK15L10LP	196603	1.5 mm	10m	101.6mm	55 mm	19 mm
SLK15L1LP	196601	1.5 mm	1m	101.6mm	55 mm	19 mm
SLK15L1LPR2	196628	1.5 mm	1m	101.6mm	55 mm	19 mm
SLK15L2LP	196514	1.5 mm	2m	101.6mm	55 mm	19 mm
SLK15L2LPR2	196629	1.5 mm	2m	101.6mm	55 mm	19 mm
SLK15L3LP	196515	1.5 mm	3m	101.6mm	55 mm	19 mm
SLK15L3LPR2	196630	1.5 mm	3m	101.6mm	55 mm	19 mm
SLK15L5LP	196516	1.5 mm	5m	101.6mm	55 mm	19 mm
SLK15L5LPR2	196631	1.5 mm	5m	101.6mm	55 mm	19 mm
SLK15L7LP	196602	1.5 mm	7m	101.6mm	55 mm	19 mm

Número de catálogo	Número do artigo	Wire Rope Diameter	Wire Rope Length	Length (L)	Altura (H)	Largura (W)
SLK2L10LP	196606	2 mm	10m	101.6mm	55 mm	19 mm
SLK2L1LP	196604	2 mm	1m	101.6mm	55 mm	19 mm
SLK2L2LP	196543	2 mm	2m	101.6mm	55 mm	19 mm
SLK2L3LP	196544	2 mm	3m	101.6mm	55 mm	19 mm
SLK2L5LP	196545	2 mm	5m	101.6mm	55 mm	19 mm
SLK2L7LP	196605	2 mm	7m	101.6mm	55 mm	19 mm
SLK3L10LP	196711	3 mm	10m	101.6mm	62 mm	24 mm
SLK3L1LP	196706	3 mm	1m	101.6mm	62 mm	24 mm
SLK3L2LP	196707	3 mm	2m	101.6mm	62 mm	24 mm
SLK3L3LP	196708	3 mm	3m	101.6mm	62 mm	24 mm

Table 2/2

Número de catálogo	Número do artigo	Wire Rope Diameter	Wire Rope Length	Length (L)	Altura (H)	Largura (W)
SLK3L5LP	196709	3 mm	5m	101.6mm	62 mm	24 mm


Table 1/2

Número de catálogo	Número do artigo	Espessura (T)	Ângulo (a)	Static Load	Certifications
SLK15L10LP	196603	12.5 mm	90 ° Max	195N	SMACNA, UL, cUL
SLK15L1LP	196601	12.5 mm	90 ° Max	195N	cUL, SMACNA, UL
SLK15L1LPR2	196628	12.5 mm	90 ° Max	195N	UL, SMACNA, cUL
SLK15L2LP	196514	12.5 mm	90 ° Max	195N	SMACNA, cUL, UL
SLK15L2LPR2	196629	12.5 mm	90 ° Max	195N	cUL, UL, SMACNA
SLK15L3LP	196515	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK15L3LPR2	196630	12.5 mm	90 ° Max	195N	cUL, UL, SMACNA
SLK15L5LP	196516	12.5 mm	90 ° Max	195N	cUL, SMACNA, UL
SLK15L5LPR2	196631	12.5 mm	90 ° Max	195N	UL, SMACNA, cUL
SLK15L7LP	196602	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK2L10LP	196606	12.5 mm	90 ° Max	440N	SMACNA, UL, cUL
SLK2L1LP	196604	12.5 mm	90 ° Max	440N	SMACNA, UL, cUL
SLK2L2LP	196543	12.5 mm	90 ° Max	440N	UL, SMACNA, cUL
SLK2L3LP	196544	12.5 mm	90 ° Max	440N	SMACNA, cUL, UL
SLK2L5LP	196545	12.5 mm	90 ° Max	440N	UL, SMACNA, cUL
SLK2L7LP	196605	12.5 mm	90 ° Max	440N	cUL, UL, SMACNA
SLK3L10LP	196711	16 mm	90 ° Max	890N	SMACNA
SLK3L1LP	196706	16 mm	90 ° Max	890N	SMACNA
SLK3L2LP	196707	16 mm	90 ° Max	890N	SMACNA

Número de catálogo	Número do artigo	Espessura (T)	Ângulo (a)	Static Load	Certifications
SLK3L3LP	196708	16 mm	90 ° Max	890N	SMACNA

Table 2/2					
Número de catálogo	Número do artigo	Espessura (T)	Ângulo (a)	Static Load	Certifications
SLK3L5LP	196709	16 mm	90 ° Max	890N	SMACNA

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

