

Metalliset reikätiivisteet

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hol-Sealers hole seals . Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick. Maintains enclosures Type rating 3R, 4, 4X (Stainless Steel version only) 12, and 13 when installed in an nVent HOFFMAN enclosure.



INDUSTRY STANDARDS

UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 (MS)

UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 (SS)

Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 12, 13

NEMA/EEMAC Type 3R, 4, 12, 13

IEC 60529, IP66

Stainless Steel Hole Seals

CSA File No. 42186; Type 3R, 4, 4X, 12, 13

NEMA/EEMAC Type 3R, 4, 4X, 12, 13

IEC 60529, IP66

FEATURES

Available in multiple colors and sizes

Oil-resistant gasket provided

Steel model has plated stud (10-32x5/8) and wing nut

Stainless steel model has 300 series stainless steel stud (10-24x5/8) and wing nut

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Color	Color Code	Thickness	Hole Diameter
AS056MSS	Stainless Steel 304	Polished			1.5mm	14mm max
AS056M	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	14mm max
AS056MFB	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	14mm max

Catalog Number	Material	Finish	Color	Color Code	Thickness	Hole Diameter
AS056MLG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	14mm max
AS056CB	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	14mm max
ASPBGSS	Stainless Steel 304	Polished			1.5mm	22mm max
ASPBG	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	22mm max
AS100LG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	35mm
AS100SS	Stainless Steel 304	Polished			1.5mm	35mm
AS100	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	35mm
AS050	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	22mm max
AS050LG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	22mm max
AS050SS	Stainless Steel 304	Polished			1.5mm	22mm max
AS350SS	Stainless Steel 304	Polished			1.5mm	105mm max
AS250SS	Stainless Steel 304	Polished			1.5mm	76mm max
AS125LG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	43mm max
AS150SS	Stainless Steel 304	Polished			1.5mm	51mm max
AS400SS	Stainless Steel 304	Polished			1.5mm	117mm max
AS125SS	Stainless Steel 304	Polished			1.5mm	43mm max
AS075	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	27mm max

Table 2/2

Catalog Number	Material	Finish	Color	Color Code	Thickness	Hole Diameter
AS150LG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	51mm max
ASPB	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	32mm max
AS300SS	Stainless Steel 304	Polished			1.5mm	92mm max
AS300	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	92mm max
AS150	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	51mm max
AS125	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	43mm max
AS400	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	117mm max
AS200	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	64mm max
ASPBSS	Stainless Steel 304	Polished			1.5mm	32mm max
AS200SS	Stainless Steel 304	Polished			1.5mm	64mm max
AS250	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	76mm max
AS075SS	Stainless Steel 304	Polished			1.5mm	27mm max
ASPB LG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	32mm max
AS350	Mild Steel	Powder Coated	Gray	ANSI 61	1.5mm	105mm max
AS200LG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	64mm max
AS075LG	Mild Steel	Powder Coated	Light Gray	RAL 7035	1.5mm	27mm max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE