


Support boîtier télescopique, embout 400-635 mm, prof. boîtier 38, 54, 63,5 mm

RÉFÉRENCE CATALOGUE

TSGB1624



The nVent CADDY Telescoping Screw Gun Box Bracket, First Means is a simple and intuitive support for mounting electrical boxes within stud wall applications. This solution delivers both traditional and retrofit mounting, which allows the bracket to bend for multiple depths and mount from both the front and back of the stud—making it ideal for when drywall has already been installed. As the first means of support, conduit can be run directly to the electrical box while ensuring a smooth, flat drywall finish with side-mount installations. The notched and clearly marked bend points make installation safe, fast and easy.

FONCTIONS

Designed for both single and multiple box mounting

Unique single-component break-apart design

Stamped inch markings and pilot holes accelerate precise box conduit mounting

Pilot holes allow for easy access with a screwdriver

Adjustable for non-standard stud spacing

Interlocking tab prevents accidental disassembly



ATTRIBUTS DU PRODUIT

Matériau: Acier

Finition: Prégalvanisé

Espacement des goujons: 400 - 635 mm

Profondeur du boîtier: 38mm;54mm;63.5mm

AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

Amérique du Nord

+1 800 753 9221

Option 1 – Service client

Option 2 – Assistance

technique

Europe

Pays-Bas :

+31 800-0200135

France :

+33 800 901 793

Europe

Allemagne :

800 1890272

Autres pays :

+31 13 5835404

APAC

Shanghai :

+ 86 21 2412 1618/19

Sydney :

+61 2 9751 8500

