


Wire Basket Tray Vertical Down



The nVent CADDY Wire Basket Tray Vertical Down maintains the proper bend radius of high-performance cables as they transition from the end or side of the cable tray. This offering enables smooth wire transfers from horizontal to vertical angles, ensuring cable integrity and optimizing organization. Easily assembled with the nVent CADDY Wire Basket Tray Splice Kit, the Vertical Down is ideal for small cable runs directed to data cabinets and enclosures. Contractors can experience optimal and reliable management for vertical cable dropouts while maintaining a seamless and visually appealing finished result.

FONCTIONS

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit


Ensures the natural bend radius of the cable is protected

Provides optimal support for high-performance data cable, up to and including fiber optic, Cat 5e, Cat 6, Cat 6A, and Cat 7

Matériau: Acier
Finition: Électro-galvanisé

SPÉCIFICATIONS

Référence catalogue	Couleur	Hauteur (H)	Largeur (W)	Longueur (L)	Rayon (R)	Poids unitaire
WBTVERTDWN		66 mm	172 mm	200mm	64.52mm	0.84 kg
WBTVERTDWNBA	Noir	66 mm	172 mm	200mm	64.52mm	0.84 kg
WBTVERTDWNWH	Blanc	66 mm	172 mm	200mm	64.52mm	0.84 kg



AVERTISSEMENT

Les produits nVent doivent être installés et utilisés uniquement comme indiqué dans les feuilles d'instructions et les documents de formation de nVent. Les feuilles d'instructions sont disponibles sur www.nvent.com et auprès de votre représentant du service client nVent. Une installation incorrecte, une mauvaise utilisation, une mauvaise application ou tout autre défaut de respect total des instructions et des avertissements de nVent peut entraîner une défaillance du produit, des dommages matériels, des blessures corporelles graves et la mort et/ou annuler votre garantie.

Amérique du Nord

+1 800 753 9221
Option 1 – Service client
Option 2 – Assistance
technique

Europe

Pays-Bas :
+31 800-0200135
France :
+33 800 901 793

Europe

Allemagne :
800 1890272
Autres pays :
+31 13 5835404

APAC

Shanghai :
+ 86 21 2412 1618/19
Sydney :
+61 2 9751 8500

