

Unità di controllo velocità ventola (kit)

CODICE A CATALOGO

20118-900

Adatto per tutti i ventilatori c.a. e le unità ventole (fino a 300 W) con connettore IEC 60320 C13 e C14 (plug & play).

Ordinare separatamente il filo di ingresso corrente/cavo di rete

CARATTERISTICHE

Il sensore esterno può essere impostato su un punto di misurazione desiderato

Uscita open-collector (parametrizzabile) ? Uscita allarme (attivo/passivo) ? Ventilatori c.c. (uscita PWM). Display remoto (tramite display digitale opzionale con pannello anteriore)

Si monta sulla guida di supporto fornita

Adatto per tutti i ventilatori CA, EC ed EC e unità ventola (fino a 300 W) con IEC 60320, connettori IEC C14 e C13

Regolazione semplice della temperatura all'accensione (con manopola e display digitale)

Il filo di ingresso corrente/cavo di rete può essere scelto in base ai requisiti del progetto: SCHUKO-UTE / IEC / BS



ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Modulo di controllo della ventola

Funziona con: Varistar CP

Materiale: Plastica

Peso netto: 0.588kg

Quantità nella confezione: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent.

Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE