

Impugnatura insertore/estrattore tipo IEL, leva nera, pulsante grigio, inferiore; 10 pezzi

CODICE A CATALOGO

20817-682

L'impugnatura dell'insertore/estrattore, tipo IEL in conformità allo standard IEEE 1101.10. Disassamento di 0,1" due di queste maniglie possono superare una singola forza della leva di 700N (per coppia).


CARATTERISTICHE

Adatto per forze di inserimento ed estrazione fino a 700 N (per coppia)

In conformità con IEEE 1101,10 e IEC 60297-3-102

È possibile montare un microinterruttore

L'offset da 0,1" viene utilizzato per PSU con SMD Plus



ATTRIBUTI DEL PRODOTTO

Quantità nella confezione: 10

Tipo di maniglia: IEL; Parte anteriore inferiore

Classificazione dell'inflammabilità: UL® 94V-0

Colore: Jet Black

Codice colore: RAL 9005

È conforme a: EN 45545-2

Profondità (D): 60.45mm

Altezza (H): 25.5mm

Materiale: Policarbonato; Lega di zinco

Tipo di prodotto: Manopola

Tipo: Insertore/Estrattore, offset di 0,1"

Larghezza (W): 19.8mm

Funziona con: Pannelli frontali

Peso lordo: 0.253kg


*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail

price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Ordinare i perni di codifica e il microinterruttore separatamente.

SCHEMI



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

