

Self-Cutting Cable Tie 22.67 kg Tensile Strength, 203.2 mm Natural 100 Count Bag

NÚMERO DE CATÁLOGO

CADTIESC8CNAP



The nVent CADDY Self-Cutting Cable Tie is a versatile, tool-free datacom solution for bundling large amounts of cables. This simple, yet innovative product features a built-in cutting blade to ensure a secure fastening and a safe, clean tie-off finish. Made from durable 6/6 nylon, the Self-Cutting Cable Tie boasts a robust 50lb/ 22Kg of tensile strength.

CARACTERÍSTICAS

Eliminates sharp edges and protects exposed skin from cuts during installation

Lock and twist to cut, no cutting tools required

Different colors including a black UV-protected version to meet specific needs

RoHS (Restriction of Hazardous Substances Directive) compliant

Halogen free

cULus Listed to UL 62275/CSA C22.2 No. 62275, UL Certified to IEC 62275



CARATERÍSTICAS DO PRODUTO

Número do artigo: 601019

Material: Nylon;Stainless Steel 301 (EN 1.4310)

Em conformidade com: IEC® 60695-2-11 (Glow Wire Test 960 °C)

Cor: Natural



Length (L): 203.2mm

Largura (W): 4.32 mm

Temperatura da instalação: 0 °C Min

Temperatura de operação: -20 to 85 °C

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com

