


PSU 19" c.a./c.c. per MicroTCA, con gestione (PM EMMC) doppia full-size

CODICE A CATALOGO

11098-547



L'alimentatore MTCA 600 è un modulo di potenza (PM) eccezionalmente efficiente per applicazioni MicroTCA. Questo alimentatore da 600 W è il più efficiente disponibile in formato full-size a doppia larghezza. Questo controller di gestione integrato PM lo rende ideale per l'uso in sistemi di comunicazione complessi che eseguono processori di ultima generazione e un numero maggiore di moduli AMC. L'alimentatore MTCA 600 fornisce l'alimentazione necessaria per 12 AMC, 2 unità di raffreddamento (CUS) e 2 MCH (Carrier Hub) MicroTCA.

CARATTERISTICHE

Doppia altezza, larghezza intera



ATTRIBUTI DEL PRODOTTO

Tipo di prodotto: Alimentazione

Tipo: Modalità commutata da 19"

Funziona con: Sistemi MicroTCA

Tensione di ingresso CA: 90 – 264V

Potenza: 600W

Numero di tensioni di uscita: 2

Tensione 1: 12V

Corrente 1: 6.8A

Tensione 2: 3.3V

Corrente 2: 0.18A

Larghezza rack: 6HP

Profondità: 186.65mm

Altezza: 148.3mm

Peso netto: 1.315kg

Quantità nella confezione: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Dati in uscita per Ta = ?25 ... 55 °C con raffreddamento forzato di 20 cfm.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

