

Kit pannello anteriore, schermato, cerniera inferiore, 6 U, 84 CV, 2,5 mm, al, anodizzato anteriore, conduttivo posteriore

CODICE A CATALOGO

20848-604

Pannello anteriore con profilo a U, parte inferiore incernierata per guarnizione in tessuto.


CARATTERISTICHE

Il pannello frontale con profilo a U può essere sganciato a un angolo di apertura di 135° (non RatiopacPRO)

Consente il montaggio su guide orizzontali

Pannello frontale a U schermato con guarnizione EMC in tessuto

Adatto per supporti (EuropacPRO) e custodie (RatiopacPRO, PropacPRO, CompacPRO)



ATTRIBUTI DEL PRODOTTO

Altezza del rack: 6U

Tipo di accessorio: Pannello frontale

Larghezza rack: 84HP

Quantità nella confezione: 1

Montaggio: A cerniera, in basso

Tipo di guarnizione: Tessuto

Finitura anteriore: Anodizzato

Finitura posteriore: Conduttivo

Bordi trattati: N.

È conforme a: CODICE 60297-3-101; IEEE 1101,1/10

Profondità (D): 2.5mm

Schermatura EMC: No (installabile in un secondo momento)



Finitura: Anodizzato; Passivato

Altezza (H): 261.8mm

Materiale: Alluminio

Tipo di prodotto: Pannello frontale

Tipo: Pannello frontale senza maniglia

Larghezza (W): 426.4mm


Peso netto: 1kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

INFORMAZIONI DI PRODOTTO AGGIUNTIVE

Il pannello anteriore può essere rimosso in posizione aperta (> 135°).

SCHEMI



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Il nostro straordinario portafoglio di marchi:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE