

nVent CADDY Pyramid Universal Support, 406 mm x 101.6 mm

NÚMERO DE CATÁLOGO

PBU16M



CARACTERÍSTICAS

Captive stainless steel nuts allow for custom attachment methods to the support base including easy attachment of stainless steel strut, threaded rod or other project-specific hardware

Foam bottom offers low abrasion interface for better roof membrane protection

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Provides superior load distribution, even with varying rooftop surfaces

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Includes square holes for creating an H-Frame with a 12" (305 mm) cross support (PBU16 only)

Base is manufactured from UV-stabilized thermoplastic material

CARATERÍSTICAS DO PRODUTO

Número do artigo: 360497

Material: Polietileno; Polypropylene; Stainless Steel 18-8 (EN 1.4305)

Temperatura: -45 to 65 °C

Static Load Safety Factor: 3:1

Comprimento 1 (L1): 406 mm

Comprimento 2 (L2): 480 mm

Altura (H): 102 mm

Largura (W): 201 mm

Tamanho da rosca (TS): M10

Número de orifícios: 2


A: 165 mm

Surface Area: 91613mm²

Static Load: 6670N

Peso unitário: 1 kg

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

