

# WBT Performance kabellade preform-T



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## KENMERKEN

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Materiaal:** Staal  
**Afwerking:** Voorgegalvaniseerd;Polyurethaan



## SPECIFICATIES

Table 1/2

| Catalogusnummer | Kleur | Hoogte (H) | Breedte (W) | Lengte (L) | Gatgrootte (HS) | Radius (R) | Gewicht eenheid |
|-----------------|-------|------------|-------------|------------|-----------------|------------|-----------------|
| WBTT2X12        |       | 50.8 mm    | 515.62 mm   | 711.2mm    | 19.05 mm        | 94.64mm    | 2.722 kg        |
| WBTT2X12BA      | Zwart | 50.8 mm    | 515.62 mm   | 711.2mm    | 19.05 mm        | 94.64mm    | 2.722 kg        |
| WBTT2X18        |       | 50.8 mm    | 668.02 mm   | 863.6mm    | 19.05 mm        | 94.64mm    | 4.536 kg        |
| WBTT2X18BA      | Zwart | 50.8 mm    | 668.02 mm   | 863.6mm    | 19.05 mm        | 94.64mm    | 4.536 kg        |

| Catalogusnummer | Kleur | Hoogte (H)            | Breedte (W) | Lengte (L) | Gatgrootte (HS) | Radius (R) | Gewicht eenheid |
|-----------------|-------|-----------------------|-------------|------------|-----------------|------------|-----------------|
| WBTT2X24        |       | 50.8 mm               | 817.88 mm   | 1013.46m m | 19.05 mm        | 94.64mm    | 7.257 kg        |
| WBTT2X24BA      | Zwart | 50.8 mm               | 817.88 mm   | 1013.46m m | 19.05 mm        | 94.64mm    | 7.257 kg        |
| WBTT2X4         |       | 50.8 mm               | 317.5 mm    | 513.08mm   |                 | 94.64mm    | 0.454 kg        |
| WBTT2X4BA       | Zwart | 50.8 mm               | 317.5 mm    | 513.08mm   |                 | 94.64mm    | 0.454 kg        |
| WBTT2X6         |       | 50.8 mm               | 365.76 mm   | 561.34mm   |                 | 94.64mm    | 1.361 kg        |
| WBTT2X6BA       | Zwart | 50.8 mm               | 365.76 mm   | 561.34mm   |                 | 94.64mm    | 1.361 kg        |
| WBTT2X8         |       | 50.8 mm               | 416.56 mm   | 612.14mm   |                 | 94.64mm    | 1.814 kg        |
| WBTT2X8BA       | Zwart | 50.8 mm               | 416.56 mm   | 612.14mm   |                 | 94.64mm    | 1.814 kg        |
| WBTT6X6         |       | 152.39999999999998 mm |             |            |                 |            |                 |
| WBTT2X4S4       |       | 50.8 mm               |             |            |                 |            |                 |
| WBTT4X12        |       | 101.6 mm              |             |            |                 |            |                 |
| WBTT4X12BA      | Zwart | 101.6 mm              |             |            |                 |            |                 |
| WBTT4X18        |       | 101.6 mm              |             |            |                 |            |                 |
| WBTT4X18BA      | Zwart | 101.6 mm              |             |            |                 |            |                 |
| WBTT4X24        |       | 101.6 mm              |             |            |                 |            |                 |
| WBTT4X24BA      | Zwart | 101.6 mm              |             |            |                 |            |                 |

Table 2/2

| Catalogusnummer | Kleur | Hoogte (H) | Breedte (W) | Lengte (L) | Gatgrootte (HS) | Radius (R) | Gewicht eenheid |
|-----------------|-------|------------|-------------|------------|-----------------|------------|-----------------|
| WBTT4X4         |       | 101.6 mm   |             |            |                 |            |                 |
| WBTT4X4BA       | Zwart | 101.6 mm   |             |            |                 |            |                 |
| WBTT4X6         |       | 101.6 mm   |             |            |                 |            |                 |
| WBTT4X6BA       | Zwart | 101.6 mm   |             |            |                 |            |                 |
| WBTT6X12        |       | 152.4 mm   |             |            |                 |            |                 |
| WBTT6X12BA      | Zwart | 152.4 mm   |             |            |                 |            |                 |
| WBTT6X18        |       | 152.4 mm   |             |            |                 |            |                 |
| WBTT6X18BA      | Zwart | 152.4 mm   |             |            |                 |            |                 |
| WBTT6X24        |       | 152.4 mm   |             |            |                 |            |                 |
| WBTT6X24BA      | Zwart | 152.4 mm   |             |            |                 |            |                 |
| WBTT6X36        |       | 152.4 mm   |             |            |                 |            |                 |

### WAARSCHUWING

---

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op [www.nvent.com](http://www.nvent.com) en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.

#### Noord-Amerika

+1.800.753.9221  
optie 1 – Klantenservice  
optie 2 – Technische  
ondersteuning

#### Europa

Nederland:  
+31 800-0200135  
Frankrijk:  
+33 800 901 793

#### Europa

Duitsland:  
800 1890272  
andere landen:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

