

Improved nVent CADDY Cat HP J-Hook



nVent CADDY Cat HP J-Hooks are the foundation of the nVent CADDY Cat HP System. The revamped nVent CADDY Cat HP J-Hook offers contractors three unique, UL-certified attachment methods out of the box—wall, ceiling, and threaded rod installations. This added functionality enables contractors to reduce SKU inventory while maintaining efficiency and continued progress on the jobsite with the most common structural attachment methods.

The modernized design of the nVent CADDY Cat HP J-Hook is engineered to provide optimal support and protection for today's rapidly evolving, high-performing low voltage cable. Contractors can feel confident utilizing the nVent CADDY Cat HP J-Hook due to its installation versatility, superior cable support and protection, and technical certifications.

CARACTERÍSTICAS

One through-hole for easier installation of threaded rod

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro (Ø)	Area	Cable Capacity, Cat 5e
CAT16HP	181061	Aço	Pregalvanized	25 mm	690mm ²	20
CAT21HP	181188	Aço	Pregalvanized	33.3 mm	1174mm ²	50
CAT48HP	181063	Aço	Pregalvanized	75 mm	5974mm ²	200
CAT64HP	181064	Aço	Pregalvanized	100 mm	9987mm ²	330
CAT32HP	181062	Aço	Pregalvanized	50 mm	2561mm ²	90

Table 2/2




Número de catálogo	Número do artigo	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Altura 1 (H1)	Altura 2 (H2)	Static Load
CAT16HP	181061	15	10	108.9mm	90.2mm	267N
CAT21HP	181188	40	25	122.2mm	103.6mm	267N
CAT48HP	181063	150	80	164.6mm	148.8mm	267N
CAT64HP	181064	220	140	188.5mm	180mm	267N
CAT32HP	181062	60	35	130.8mm	112.3mm	267N

DETALHES ADICIONAIS DO PRODUTO

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência

técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

