

nVent CADDY Macrofix Insulated Ventilation Duct Clamp



CARACTERÍSTICAS

Complete hanger assembly comes out of the box ready to install (sizes up to 600 mm)

Increased opening angle easily accommodates all standard-sized spiral ducts (sizes up to 600 mm)

Quick locking system prevents the hanger from accidentally opening when duct is moved or adjusted (sizes up to 600 mm)

Quick locking system easily closes with one hand (sizes up to 600 mm)

Thread impression retains quick locking captive screw and prevents it from falling out during installation

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Halogen-free

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

Material: EPDM-SBR Rubber;Aço
Acabamento: Electrogalvanized
Temperatura: -50 to 110 °C




ESPECIFICAÇÕES

Table 1/2						
Número de catálogo	Número do artigo	Diâmetro externo (OD)	Tamanho da haste (RS)	Largura (W)	Espessura (T)	Diâmetro do Parafuso (Sc)
MFVI0080EG	586601	80 mm	M8, M10	20 mm	1 mm	6
MFVI0100EG	586603	100 mm	M8, M10	20 mm	1 mm	6
MFVI0125EG	586605	125 mm	M8, M10	20 mm	1 mm	6
MFVI0140EG	586606	140 mm	M8, M10	20 mm	1 mm	6
MFVI0150EG	586607	150 mm	M8, M10	20 mm	1 mm	6
MFVI0160EG	586608	160 mm	M8, M10	20 mm	1 mm	6
MFVI0200EG	586610	200 mm	M8, M10	20 mm	1 mm	6
MFVI0250EG	586612	250 mm	M8, M10	21 mm	1.25 mm	6
MFVI0300EG	586614	300 mm	M8, M10	21 mm	1.25 mm	6
MFVI0315EG	586615	315 mm	M8, M10	21 mm	1.25 mm	6
MFVI0355EG	586616	355 mm	M8, M10	21 mm	1.25 mm	6
MFVI0400EG	586617	400 mm	M8, M10	21 mm	1.25 mm	6
MFVI0450EG	586618	450 mm	M8, M10	21 mm	1.5 mm	6
MFVI0500EG	586619	500 mm	M8, M10	21 mm	1.5 mm	6
MFVI0560EG	586620	560 mm	M8, M10	21 mm	1.5 mm	6
MFVI0600EG	586621	600 mm	M8, M10	21 mm	1.5 mm	6
MFVI0630EG	586622	630 mm	M8, M10	23 mm	1.75 mm	6
MFVI0710EG	586623	710 mm	M8, M10	23 mm	1.75 mm	6
MFVI0800EG	586624	800 mm	M8, M10	23 mm	1.75 mm	6
MFVI0900EG	586625	900 mm	M8, M10	23 mm	1.75 mm	6

Table 2/2				
Número de catálogo	Número do artigo	Comprimento do parafuso (L)	Ângulo (a)	Static Load
MFVI0080EG	586601	27mm	80 °	775N
MFVI0100EG	586603	27mm	80 °	775N
MFVI0125EG	586605	27mm	80 °	775N
MFVI0140EG	586606	40mm	80 °	775N
MFVI0150EG	586607	40mm	80 °	775N
MFVI0160EG	586608	40mm	80 °	775N
MFVI0200EG	586610	40mm	80 °	775N
MFVI0250EG	586612	40mm	80 °	1000N
MFVI0300EG	586614	40mm	80 °	1000N
MFVI0315EG	586615	40mm	80 °	1000N
MFVI0355EG	586616	40mm	80 °	1000N

Número de catálogo	Número do artigo	Comprimento do parafuso (L)	Ângulo (a)	Static Load
MFVI0400EG	586617	40mm	80 °	1000N
MFVI0450EG	586618	40mm	80 °	1400N
MFVI0500EG	586619	40mm	80 °	1400N
MFVI0560EG	586620	40mm	80 °	1400N
MFVI0600EG	586621	40mm	80 °	1400N
MFVI0630EG	586622	40mm		1900N
MFVI0710EG	586623	40mm		1900N
MFVI0800EG	586624	40mm		1900N
MFVI0900EG	586625	40mm		1900N

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

