

# nVent CADDY Speed Link SLK with Decking Hook



## CARACTERÍSTICAS

Complete system includes wire, locking device and pre-assembled decking hook end fitting

Quickly and easily attaches to hollow metal decking

Spring-loaded ends snap into decking hole and lock into place

Innovative design helps protect the wire from sharp edges of decking hole, minimizing risk of damage to wire

**Material:** Aço; Liga de zinco; Polypropylene  
**Acabamento:** Electrogalvanized  
**Static Load Safety Factor:** 5:1  
**Em conformidade com:** SMACNA HVAC-DCS



## ESPECIFICAÇÕES

| Número de catálogo | Número do artigo | Wire Rope Diameter | Wire Rope Length | Roof Decking Sheet Thickness | A      | Tamanho do orifício (HS) | Static Load |
|--------------------|------------------|--------------------|------------------|------------------------------|--------|--------------------------|-------------|
| SLK15L1DH          | 196676           | 1.5 mm             | 1m               | 1.5 mm Max                   | 9.2 mm | 8 mm                     | 195N        |
| SLK15L2DH          | 196677           | 1.5 mm             | 2m               | 1.5 mm Max                   | 9.2 mm | 8 mm                     | 195N        |
| SLK15L3DH          | 196504           | 1.5 mm             | 3m               | 1.5 mm Max                   | 9.2 mm | 8 mm                     | 195N        |
| SLK15L5DH          | 196505           | 1.5 mm             | 5m               | 1.5 mm Max                   | 9.2 mm | 8 mm                     | 195N        |
| SLK2L3DH           | 196532           | 2 mm               | 3m               | 1.5 mm Max                   | 9.2 mm | 8 mm                     | 440N        |
| SLK2L5DH           | 196533           | 2 mm               | 5m               | 1.5 mm Max                   | 9.2 mm | 8 mm                     | 440N        |


|                       |          |
|-----------------------|----------|
| <b>Altura (H):</b>    | 55 mm    |
| <b>Largura (W):</b>   | 19 mm    |
| <b>Espessura (T):</b> | 12.5 mm  |
| <b>Ângulo (a):</b>    | 90 ° Max |

## DETALHES ADICIONAIS DO PRODUTO

Load rating is only applicable if the load-bearing capacity of the supporting element (steel decking) is adequate.

Check with deck manufacturer for recommended load capacity.

## DIAGRAMAS



## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

#### **América do Norte**

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência  
técnica

#### **Europa**

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

#### **Europa**

Alemanha:

800 1890272

Outros países:

+31 13 5835404

#### **APAC**

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

