

Front Panel Kit, Shielded, Bottom Hinged, 6 U, 42 HP, 2.5 mm, Al, Front Anodized, Rear Conductive

NÚMERO DE CATÁLOGO

20848-602

U-profile front panel bottom hinged for textile gasket.


CARACTERÍSTICAS

U-profile front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

Shielded, U front panel with textile EMC gasket

Suitable for subracks (EuropacPRO) and cases (RatiopacPRO, PropacPRO, CompacPRO)



CARATERÍSTICAS DO PRODUTO

Rack Height: 6U

Accessory Type: Front panel

Rack Width: 42HP

Quantidade por embalagem: 1

Instalação: Hinged, Bottom

Gasket Type: Textile EMC

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Não

Em conformidade com: IEC 60297-3-101; IEEE 1101.1/10

Profundidade (D): 2.5mm

EMC Shielding: No (Retrofittable)

Acabamento: Anodized; Passivated



Material: Aluminio

Tipo: Front Panel without Handle

Gross Weight: 0.586kg

DETALHES ADICIONAIS DO PRODUTO

DIAGRAMAS



North America

Europe

Asia

Middle East & India



CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE