

EDGE -48VDC PDU 4X35A OG 4X60A



KATALOGNUMMER

21280-002

nVent Edge-DC-48VDC Power Distribution Unit (DCDU) er utformet for å gi effektiv, sikker og pålitelig strømdistribusjon for telekom og edge computing miljøer. Denne enheten sikrer optimal ytelse og beskyttelse for kritisk infrastruktur.

FUNKSJONER

Høy effektkapasitet: Robust 250 A 48 VDC-inngang

Kapasitet for blind mating: Støtter byttet og målt DC moduler fra 10 A til 60 A

Kjørealarm for automatsikring: Umiddelbar varsling for å øke responstiden

Overholdelse av bransjestandarder: UL/CE-sertifisert

Brytere som kan byttes ut med nøyaktig måling: For energi, strøm, strøm og spenning på både inngangsnivå og enhetsnivå

Detaljert kontroll med enhetsnivåveksling: Administrasjon av individuelle enheter for optimal ytelse

Overvåking av faktureringsgrad: Identifisering av potensielle systemfeil

Smart alarmsystem: Informerer om overstrøm, overspenning, underspenning og andre terskelbrudd

Grensesnitt for styreenhet: TCP- eller IP-nettverkstilkobling

Lokal forvaltning: Har frontpanel-knapp for å veksle modulutgang. Panel status LED-indikator sender raskt modulinformasjon til lokal bruker



PRODUKTEGENSKAPER

Produkttype: Strømfordeler

Kretsbytter: - 48 VDC 60 Amp; - 48 VDC 35 Amp

Kretsbytermengde: 8

Dybde: 410mm

Inngangsspenning DC: -48V min

Målingstype: Utløp

Antall vekslede uttak: (4) 60 A; (4) 35 A

Rackhøyde: 3U

Rackbredde: 84HP

Type: - 48 V DCDU

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Se tabellen(e) som leveres for nøyaktig konfigurasjon.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

