

VPX bakplan, 3 U, 5 spor, full-Mesh, med RTM

KATALOGNUMMER

23001-813

nVent SCHROFF VPX-bakplanet har utmerket signalintegritet for høyeste dataoverføringshastighet.

FUNKSJONER

I samsvar med: VITA 46,0 VPX base standard; VITA 46,3 Serial RapidIO på VPX; Vita 46,4 PCI Express på VPX Fabric Connector; VITA 46,7 Ethernet på VPX Fabric Connector; VITA 46,11 System Management for VPX

DIP-bryter for systemsporinnstillinger

JTAG-forbindelser

Låsbare aux-verktøy og SENSE-kontakter

M4 strømbolter for strømforsyning, maks. 22 A per spor for hver spenning



PRODUKTEGENSKAPER

Produkttype: Sentralenhet

Antall spor: 5

Rackhøyde: 3U

Bakplantype: VPX med full duk

Sporbredde: 4HP

Kontakttype: MultiGig

Strømkontakttype: Trykknapper M4

Type strømkontakt: Microfit, 8-pinner

Bredde: 120.67mm

Nettvekt: 0.53kg

Antall pakker: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address,

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGERE PRODUKTDETALJER

Andre VPX-bakplan og tilpassede VPX-bakplandesign på forespørsel.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE