

Zasilacz 19" AC/DC dla MicroTCA, z funkcją zarządzania (PM EMMC), podwójny pełny rozmiar

NUMER KATALOGOWY

11098-547



MTCA PSU 600 to wyjątkowo wydajny moduł zasilania (PM) do zastosowań MicroTCA. Ten zasilacz o mocy 600 W jest najbardziej wydajny w formacie pełnowymiarowym o podwójnej szerokości. Ten zintegrowany kontroler zarządzania PM idealnie nadaje się do stosowania w złożonych systemach komunikacyjnych z najnowszą generacją procesorów i zwiększoną liczbą modułów AMC. Zasilacz MTCA 600 zapewnia zasilanie wymagane dla 12 kontrolerów AMC, 2 jednostek chłodzących (CUS) i 2 koncentratorów nośnych MicroTCA (MChS).

FUNKCJE

Podwójna wysokość pełnowymiarowa szerokość



ATRYBUTY PRODUKTU

Typ produktu: Zasilanie

Typ: Tryb impulsowy 19"

Współpracuje z: Systemy MicroTCA

Napięcie wejściowe AC: 90 – 264V

Zasilanie: 600W

Liczba napięć wyjściowych: 2

Napięcie 1: 12V

Prąd 1: 6.8A

Napięcie 2: 3.3V

Prąd 2: 0.18A

Szerokość stojaka: 6HP

Głębokość: 186.65mm

Wysokość: 148.3mm

Waga netto: 1.315kg

Liczba opakowań: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Dane wyjściowe dla Ta = 25 ... 55 °C z wymuszonym chłodzeniem 20 cfm.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE