

System PXI z zasilaczem ATX, 4 U, 8 gniazd, 44 km

NUMER KATALOGOWY

14579-008

Obudowa typu desktop PXI z pionową obudową na osiem płyt 3 U i wbudowanym zasilaczem.

FUNKCJE

System zgodny z IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11); płyta montażowa, zgodny z PICMG rev. 3.0 i PXI 2.0

Obudowa biurkowa PXI, 4 U, 44 km z pionową obudową na karty. Format płyty przód: 3U, 160 mm

Płyta montażowa, 8 gniazdo, 3 HE, 64 bit, gniazdo systemowe z lewej strony

Rozpraszanie ciepła z przepływem powietrza od dołu do tyłu

Zasilanie ATX 400 w, wejście AC o szerokim zakresie z przełącznikiem zasilania z tyłu

Płyta montażowa z przełączaniem zegara wewnętrznego / zewnętrznego



ATRYBUTY PRODUKTU

Typ produktu: System

Liczba szczelin: 8

Typ: Desktop

Typ płyty montażowej: 3 U CompactPCI z PXIbus

Transfer danych: 64-bitowa magistrala PCI

Moc na szczelinę: 30W

Napięcie wejściowe AC: 100 – 240V

Kierunek przepływu powietrza: Od dołu do tyłu

Wysokość stojaka: 4U

Typ zasilacza: Otwarta rama

Zasilacz w zestawie: Tak

Tylne We/Wy: Nie

Zgodność z: PXISA PXI-1 R2.0

Głębokość: 355mm

Waga netto: 9.6kg

Liczba opakowań: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Zmodyfikowane systemy dostępne na życzenie.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE