


Zestaw panelu przedniego, ekranowany, na zawiasach dolny, 6 U, 42 HP, 2.5 mm, Al, z przodu anodyzowany, z tyłu przewodzący



NUMER KATALOGOWY

20848-602

Dolny panel przedni z profilem U na zawiasach dla uszczelki tekstylnej.

FUNKCJE

Panel przedni z profilem U można odczepić pod kątem otwarcia 135° (nie RatiopacPRO)

Umożliwia montaż na szynach poziomych

Ekranowany panel przedni U z tekstylną uszczelką EMC

Nadaje się do podstawek (EuropacPRO) i skrzynek (RatiopacPRO, PropacPRO, CompacPRO)



ATRYBUTY PRODUKTU

Wysokość stojaka: 6U

Typ akcesorium: Panel przedni

Szerokość stojaka: 42HP

Liczba opakowań: 1

Montaż: Na zawiasach, na dole

Typ uszczelki: Tekstylna

Wykończenie z przodu: Anodyzowany

Wykończenie z tyłu: Przewodzące

Obrabiane krawędzie: Nie

Zgodność z: IEC 60297-3-101; IEEE 1101.1/10

Głębokość (D): 2.5mm

Ekranowanie EMC: Nie (możliwość modernizacji)

Wykończenie: Anodyzowany; Powierzchnia pasywowana

Wysokość (H): 261.8mm

Typ produktu: Panel przedni

Szerokość (W): 213mm

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

Panel przedni można zdjąć w położeniu otwarcia ($> 135^\circ$).

Technical drawing of a rectangular plate with the following dimensions and features:

- Overall width: A
- Overall height: H
- Top edge features:
 - Left corner: 7.45 (horizontal) and 3 (vertical)
 - Right corner: 3 (horizontal) and $M2.5$ (vertical)
- Internal features:
 - Top edge: C (distance from right corner to start of cutout)
 - Bottom edge: D (distance from left corner to start of cutout), $B - 25.4$ (total width of cutout area), and 3.1 (width of cutout)
 - Left edge: 15.6 (distance from top corner to start of cutout), 16 (width of cutout), and 8.2 (height of cutout)
- Material and finish: $\phi 5.9 \times 3.3$ (top left corner), $M2.5$ (bottom right corner)
- Section lines: $X-X$ and $Y-Y$

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Straubenhardt, Germany
 +49.7082.794.0
 Betschdorf, France
 +33.3.88.90.64.90
 Warsaw, Poland
 +48.22.209.98.35
 Assago, Italy
 +39.02.932.7141
 Chat with us:
nvent.com/schroff

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Ten dokument jest generowany przez system.