

# Front Panel, Front Anodized, Rear Conductive, Unshielded

Front panel, unshielded, front anodized and rear conductive.

## CARACTERISTICAS

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive



**Profundidade (D):** 2.5mm  
**Material:** Alumínio  
**Acabamento:** Anodized; Passivated  
**Accessory Type:** Front panel  
**Product Type:** Front Panel  
**Tipo:** Front Panel without Handle



## ESPECIFICAÇÕES

Table 1/3

| Número de catálogo | Rack Height | Rack Width | Quantidade por embalagem | Instalação     | Front Finish | Rear Finish |
|--------------------|-------------|------------|--------------------------|----------------|--------------|-------------|
| 30847-470          | 3U          | 2HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-464          | 4U          | 63HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-480          | 9U          | 8HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-125          | 6U          | 5HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-148          | 6U          | 28HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-183          | 6U          | 63HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-047          | 3U          | 8HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-067          | 3U          | 28HP       | 1                        | Screw-on Front | Anodized     | Conductive  |

| Número de catálogo | Rack Height | Rack Width | Quantidade por embalagem | Instalação     | Front Finish | Rear Finish |
|--------------------|-------------|------------|--------------------------|----------------|--------------|-------------|
| 30847-476          | 4U          | 4HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-127          | 6U          | 7HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-468          | 5U          | 63HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-463          | 4U          | 42HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-471          | 3U          | 3HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-046          | 3U          | 7HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-128          | 6U          | 8HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-126          | 6U          | 6HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-045          | 3U          | 6HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-130          | 6U          | 10HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-469          | 5U          | 84HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-081          | 3U          | 42HP       | 1                        | Screw-on Front | Anodized     | Conductive  |

Table 2/3

| Número de catálogo | Rack Height | Rack Width | Quantidade por embalagem | Instalação     | Front Finish | Rear Finish |
|--------------------|-------------|------------|--------------------------|----------------|--------------|-------------|
| 30838-123          | 3U          | 84HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-460          | 2U          | 63HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-141          | 6U          | 21HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-462          | 4U          | 28HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-132          | 6U          | 12HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-044          | 3U          | 5HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-043          | 3U          | 4HP        | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-136          | 6U          |            | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-134          | 6U          | 14HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-102          | 3U          | 63HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-467          | 5U          | 42HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-053          | 3U          | 14HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-459          | 2U          | 42HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-556          | 9U          | 84HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-458          | 2U          | 28HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-055          | 3U          | 16HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-162          | 6U          | 42HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-204          | 6U          | 84HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-484          | 9U          | 12HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-465          | 4U          | 84HP       | 1                        | Screw-on Front | Anodized     | Conductive  |

Table 3/3

| Número de catálogo | Rack Height | Rack Width | Quantidade por embalagem | Instalação     | Front Finish | Rear Finish |
|--------------------|-------------|------------|--------------------------|----------------|--------------|-------------|
| 30838-051          | 3U          | 12HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-060          | 3U          | 21HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-466          | 5U          | 28HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-461          | 2U          | 84HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-049          | 3U          | 10HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30847-482          | 9U          | 10HP       | 1                        | Screw-on Front | Anodized     | Conductive  |
| 30838-124          | 6U          | 4HP        | 1                        | Screw-on Front | Anodized     | Conductive  |

Table 1/3

| Número de catálogo | Treated Edges | Em conformidade com             | EMC Shielding | Altura (H) | Largura (W) | Certifications |
|--------------------|---------------|---------------------------------|---------------|------------|-------------|----------------|
| 30847-470          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 9.8mm       | RoHS           |
| 30847-464          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 172.9mm    | 319.7mm     | RoHS           |
| 30847-480          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 395.1mm    | 40.3mm      | RoHS           |
| 30838-125          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 25mm        | RoHS           |
| 30838-148          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 141.9mm     | RoHS           |
| 30838-183          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 319.7mm     | RoHS           |
| 30838-047          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 40.3mm      | RoHS           |
| 30838-067          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 141.9mm     | RoHS           |
| 30847-476          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 395.1mm    | 20mm        | RoHS           |
| 30838-127          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 35.2mm      | RoHS           |
| 30847-468          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 217.4mm    | 319.7mm     |                |
| 30847-463          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 172.9mm    | 213mm       | RoHS           |
| 30847-471          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 14.9mm      | RoHS           |
| 30838-046          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 35.2mm      | RoHS           |

| Número de catálogo | Treated Edges | Em conformidade com             | EMC Shielding | Altura(H) | Largura(W) | Certifications |
|--------------------|---------------|---------------------------------|---------------|-----------|------------|----------------|
| 30838-128          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm   | 40.3mm     | RoHS           |
| 30838-126          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm   | 30.1mm     | RoHS           |
| 30838-045          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm   | 30.1mm     | RoHS           |
| 30838-130          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm   | 50.5mm     | RoHS           |
| 30847-469          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 217.4mm   | 426.4mm    |                |
| 30838-081          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm   | 213mm      | RoHS           |

Table 2/3

| Número de catálogo | Treated Edges | Em conformidade com             | EMC Shielding | Altura (H) | Largura (W) | Certifications |
|--------------------|---------------|---------------------------------|---------------|------------|-------------|----------------|
| 30838-123          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 426.4mm     | RoHS           |
| 30847-460          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 84mm       | 319.7mm     |                |
| 30838-141          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 106.3mm     | RoHS           |
| 30847-462          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 172.9mm    | 141.9mm     |                |
| 30838-132          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 60.6mm      | RoHS           |
| 30838-044          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 25mm        | RoHS           |
| 30838-043          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 20mm        | RoHS           |
| 30838-136          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 80.9mm      | RoHS           |
| 30838-134          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 70.8mm      | RoHS           |
| 30838-102          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 319.7mm     | RoHS           |
| 30847-467          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 217.4mm    | 213mm       |                |
| 30838-053          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 70.8mm      | RoHS           |



| Número de catálogo | Treated Edges | Em conformidade com             | EMC Shielding | Altura(H) | Largura(W) | Certifications |
|--------------------|---------------|---------------------------------|---------------|-----------|------------|----------------|
| 30847-459          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 84mm      | 213mm      |                |
| 30847-556          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 395.1mm   | 426.4mm    | RoHS           |
| 30847-458          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 84mm      | 141.9mm    |                |
| 30838-055          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm   | 80.9mm     | RoHS           |
| 30838-162          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm   | 213mm      | RoHS           |
| 30838-204          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm   | 426.4mm    | RoHS           |
| 30847-484          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 395.1mm   | 60.6mm     | RoHS           |
| 30847-465          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 172.9mm   | 426.4mm    | RoHS           |

Table 3/3

| Número de catálogo | Treated Edges | Em conformidade com             | EMC Shielding | Altura (H) | Largura (W) | Certifications |
|--------------------|---------------|---------------------------------|---------------|------------|-------------|----------------|
| 30838-051          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 60.6mm      | RoHS           |
| 30838-060          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 106.3mm     | RoHS           |
| 30847-466          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 217.4mm    | 141.9mm     |                |
| 30847-461          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 84mm       | 426.4mm     | RoHS           |
| 30838-049          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 128.4mm    | 50.5mm      | RoHS           |
| 30847-482          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 395.1mm    | 50.5mm      | RoHS           |
| 30838-124          | Não           | IEC 60297-3-101, IEEE 1101.1/10 | Não           | 261.8mm    | 20mm        | RoHS           |

## DETALHES ADICIONAIS DO PRODUTO

Please order fixing material (sleeves, collar screws) separately.



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



O nosso forte portefólio de marcas:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE