

Kontroler PXI Express, 4 km, I3-1115G4E 16-512

NUMER KATALOGOWY

21265-120



Wbudowany kontroler nVent SCHROFF PXIe jest najbardziej kompaktowym i wydajnym kontrolerem wbudowanym 3U dla platform PXI Express i CPClexp. Dzięki ogromnym i przyszłościowym możliwościom interfejsu, działa doskonale z większością aplikacji testowych i pomiarowych. Kontroler jest napędzany przez procesory Intel® Core™ I3/i5 11. Generacji w połączeniu z pamięcią DDR4 o pojemności do 64 GB i z łatwością obsługuje aplikacje o dużej przepustowości dzięki gotowej na przyszłość technologii PCIe Gen4 i podwójnemu połączeniu z systemem 2500BASE-T.

FUNKCJE

Kontroler systemowy PXI Express, 3 U, 4 km, z procesorem Intel Core I3-1115G4E

PXI-5 PXI Express specyfikacja sprzętowa Zgodność z rev.2.0

Maksymalna przepustowość PCIe 14 GB/s.

Możliwość rozbudowy pamięci masowej M.2 NVMe i DDR4

3x USB3.1, 2x GbE i 1x DP 1.2 na panelu przednim

W pełni konfigurowalny system BIOS AMI Aptio® Embedded

ATRYBUTY PRODUKTU

Typ produktu: System

Typ: Sterownik

Transfer danych: PCIe Gen3

Wysokość stojaka: 3U

Zgodność z: PXISA PXI-5 R1.1

Głębokość: 160mm

Waga brutto: 0.548kg

Liczba opakowań: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Zgodność z PICMG rev. 3.0 i PXI-5.

Zmodyfikowane kontrolery dostępne na życzenie.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE