


# MTCA.4 Front Panel



AdvancedTCA front panel (stainless steel) for textile gasketing. Shielded filler modules are used to close unused slots.

## CARACTERÍSTICAS

In accordance with MicroTCA.1 and MicroTCA.4 specifications

Shielded filler modules are used to close unused slots

Can be screwed on; is supported on the guide rail

|                             |                |
|-----------------------------|----------------|
| <b>Accessory Type:</b>      | Front panel    |
| <b>EMC Shielding:</b>       | Sim            |
| <b>Material:</b>            | Aço inoxidável |
| <b>Família de produtos:</b> | AdvancedMC     |
| <b>Product Type:</b>        | Front Panel    |
| <b>Tipo:</b>                | Front Panel    |



## ESPECIFICAÇÕES

Table 1/2

| Número de catálogo | Altura  | Rack Width | Quantidade por embalagem | Instalação     | Gasket Type | Front Finish |
|--------------------|---------|------------|--------------------------|----------------|-------------|--------------|
| 21850-102          | 84.68mm |            | 1                        | Screw-on Front | Textile EMC | Raw          |
| 21850-103          | 84.68mm |            | 1                        | Screw-on Front | Textile EMC | Raw          |
| 20849-213          | 95mm    | 2HP        | 1                        | Screw-on Front | Textile EMC | Raw          |
| 20849-214          | 170mm   | 2HP        | 1                        | Screw-on Front | Textile EMC | Raw          |

Table 2/2

| Número de catálogo | Rear Finish | Profundidade | Largura |
|--------------------|-------------|--------------|---------|
| 21850-102          | Raw         | 1mm          | 18.96mm |
| 21850-103          | Raw         | 1mm          | 28.98mm |
| 20849-213          | Raw         | 0.6mm        | 8.8mm   |
| 20849-214          | Raw         | 0.6mm        | 8.8mm   |

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

