

# Plug-In Unit Kit With IET Handle, Shielded, Black 3 U



Plug-in unit, with IET inserter/extractor black handle, 3 U, front assembly. The U-shaped front panel enable shielding with a textile gasket.

## CARACTERÍSTICAS

U-shaped front panel for textile gasket

Suitable for insertion and extraction forces up to 700 N (per pair)

Enable the installation of a microswitch

Enable the installation of coding pegs in accordance with IEC 60297-3-103/ IEEE 1101.10

|                       |                               |
|-----------------------|-------------------------------|
| <b>EMC Shielding:</b> | Sim                           |
| <b>Acabamento:</b>    | Anodized; Passivated          |
| <b>Material:</b>      | Aluminio                      |
| <b>Product Type:</b>  | Front Panel                   |
| <b>Rack Height:</b>   | 3U                            |
| <b>Tipo:</b>          | Front Panel with Handle (PIU) |



## ESPECIFICAÇÕES

Table 1/2

| Número de catálogo | Rack Width | Quantidade por embalagem | Tipo de alça | Instalação     | Gasket Type | Front Finish |
|--------------------|------------|--------------------------|--------------|----------------|-------------|--------------|
| 20848-763          | 4HP        | 1                        | IET          | Screw-on Front | Textile EMC | Anodized     |
| 20848-764          | 8HP        | 1                        | IET          | Screw-on Front | Textile EMC | Anodized     |
| 20848-765          | 12HP       | 1                        | IET          | Screw-on Front | Textile EMC | Anodized     |

Table 2/2

| Número de catálogo | Rear Finish | Treated Edges | Em conformidade com                                            | Altura   | Largura |
|--------------------|-------------|---------------|----------------------------------------------------------------|----------|---------|
| 20848-763          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | 128.4m m | 20mm    |

| Número de catálogo | Rear Finish | Treated Edges | Em conformidade com                                            | Altura      | Largura    |
|--------------------|-------------|---------------|----------------------------------------------------------------|-------------|------------|
| 20848-764          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | 128.4m<br>m | 40.3m<br>m |
| 20848-765          | Etched      | Não           | IEC 60297-3-102, IEEE 1101.10, IEC 60297-3-103, IEEE 1101.1/11 | 128.4m<br>m | 60.6m<br>m |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.