

Rack Safety Plus, 3 U, 208 / 240 V AC, filtr EMC

NUMER KATALOGOWY

21272-001

FUNKCJE

Moduł dystrybucji zasilania 19", 3 U z funkcją zatrzymania awaryjnego

Dostarcza zasilanie sieciowe do urządzeń elektrycznych lub elektronicznych jako centralny wyłącznik zasilania

208 V faza do fazy lub faza do położenia neutralnego lub 240 V faza do wejścia zasilania fazowego

Wyjścia prądu przemiennego z różnymi typami złączy, przełączane przełącznikiem ON/OFF

Stałe wyjścia prądu przemiennego (Service)

Wszystkie wyjścia są chronione przez wyłączniki automatyczne

Funkcja zatrzymania awaryjnego spełnia wymagania norm EN 60947-5-1 i EN 60204-1 i jest odporna na akty wandalizmu

Do systemu można podłączyć dodatkowy zewnętrzny przycisk zatrzymania awaryjnego

UL oczekujące



ATRYBUTY PRODUKTU

Typ produktu: Dystrybutor zasilania

Współpracuje z: Varistar CP; Novastar

Funkcja: Zatrzymanie awaryjne

Napięcie wejściowe AC: 208 – 240V

Liczba faz: 1

Filtr EMC: Tak

Filtr przeciwprzepięciowy: Tak

Ogranicznik prądu rozruchowego: Nie

Urządzenie różnicowoprądowe: Nie

Pokrywa wyłącznika obwodu: Nie

Wysokość stojaka: 3U

Typ gniazda: IEC C13; IEC C19

Typ akcesorium: Akcesoria do dystrybucji zasilania

Waga brutto: 16kg

Liczba opakowań: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Aby uzyskać dokładną konfigurację opcjonalnych funkcji i przykładową konfigurację, zapoznaj się z tabelą dostarczonych elementów.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE