

System CPCI do wtykowego zasilacza, poziomy, 3 U, 6 gniazda

NUMER KATALOGOWY

24579-080

System CompactPCI 3 U z poziomą obudową na sześć płyt 6 U, sześć płyt RTM i jeden zasilacz CompactPCI 3 U. Możliwość montażu maksymalnie trzech zasilaczy.

FUNKCJE

Zgodnie z IEC 60297-3-101, 102, 103; IEEE 1101.1, 1101.10/11; płyta montażowa zgodnie z PICMG 2.0 rev. 3.0

System z poziomą klatką kart. Format płyty przód: 6 U, głębokość 160 mm; tylne wejścia/wyjścia: 6 U, głębokość 80 mm

Płyta montażowa (płyta montażowa sygnału i zasilania w jednym urządzeniu) 6 gniazdo, 6 U, 64 bit, lewe gniazdo systemowe, złącze zasilania (2 x P 47)

Rozpraszanie ciepła przez zespół wentylatora wymiennego podczas pracy (przepływ powietrza od lewej do prawej)

Przygotowany do montażu 19-calowego zasilacza CompactPCI (3 U, 8 HP)



ATRYBUTY PRODUKTU

Typ produktu: System

Liczba szczelin: 6

Typ: Montaż w stojaku 19"

Typ płyty montażowej: 6 U CompactPCI

Transfer danych: 64-bitowa magistrala PCI

Moc na szczelinę: 40W

Napięcie wejściowe AC: 100 – 240V

Kierunek przepływu powietrza: Od lewej do prawej

Wysokość stojaka: 3U

Typ zasilacza: (1) Podłączany zasilacz

Zasilacz w zestawie: Nie

Tylne We/Wy: Tak

Zgodność z: PICMG 2.0 R3.0

Głębokość: 275mm

Wysokość: 132.5mm

Szerokość: 449mm

Waga netto: 8.57kg

Liczba opakowań: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Zmodyfikowane systemy dostępne na życzenie.

Wersja 48 VDC na żądanie.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE