


System CPCI z wtykowym zasilaczem, 4 U, 8 gniazdo



NUMER KATALOGOWY

24579-260

System CompactPCI 4 U z pionową obudową na osiem płyt 3U, osiem płyt RTM i jeden zasilacz 3U.

FUNKCJE

Zgodnie z IEC 60297-3-101, 102, 103; IEEE 1101.1, 1101.10/11; płyta montażowa zgodnie z PICMG 2.0 rev. 3.0

System z pionową klatką na karty. Format płyty przód: 3 U, głębokość 160 mm; tylne wejścia/wyjścia: 3 U, głębokość 80 mm

Płyta montażowa 8 gniazdo, 3 U, 32 bit; gniazdo systemowe po prawej stronie; można używać procesora o szerokości 8 HP; płyta montażowa zasilania

Rozpraszanie ciepła przez jednostkę wentylatora wymienianego na gorąco, przepływ powietrza od dołu do góry

ZASILACZ 19", 300 W, 3 U, 8 KM

Opcja montażu dysku twardego



ATRYBUTY PRODUKTU

Typ produktu: System

Liczba szczelin: 8

Typ: Montaż w stojaku 19"

Typ płyty montażowej: 3 U CompactPCI

Transfer danych: 32-bitowa magistrala PCI

Moc na szczelinę: 40W

Napięcie wejściowe AC: 100 – 240V

Kierunek przepływu powietrza: Od dołu do góry

Wysokość stojaka: 4U

Typ zasilacza: (1) Podłączany zasilacz

Zasilacz w zestawie: Tak

Tylne We/Wy: Tak

Zgodność z: PICMG 2.0 R3.0

Głębokość: 275mm

Wysokość: 177mm

Waga netto: 11.23kg

Liczba opakowań: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

DODATKOWE INFORMACJE O PRODUKCIE

Zmodyfikowane systemy dostępne na życzenie.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE