


Szyna pozioma, przód, typ R-LD, Wytrzymała, Długa krawędź , 28 km

NUMER KATALOGOWY

34566-328



Combinations of horizontal rails and side panels

$\text{H}^{100} + \text{H}^{100}$ can be combined, $\text{H}^{100} + \text{combination rail}$ not recommended

	Support #1	Support #2	Support #3	Support #4
Support #1		-	side rail H100 2x 100	side rail H100 2x 100
Support #2		+	side rail H100 2x 100	+
Support #3		side rail H100 2x 100	side rail H100 2x 100	+
Combination rail		-	-	-
Side panel				
	Support #1	Support #2	Support #3	Support #4

Side Panel options

Wytrzymała szyna pozioma może wytrzymać wstrząsy i wibracje do 25 g. umożliwia stosowanie uchwytów IEEE.

FUNKCJE

Wzmocnione szyny poziome typu R-LD z mocowaniem 3-
otworowym zwiększającym wytrzymałość

Do wkładania/ekstrakcji płyt CompactPCI lub VME64x

Z urządzeniami HP drukowanymi od 28 km do góry

Długość 20, 28, 40, 42, 63, 84 HP lub 1000 mm

Wyłaczanie aluminium, anodowane wykończenie,
przewodząca powierzchnia kontaktowa, z oznaczeniami
HP



ATRYBUTY PRODUKTU

Szerokość stojaka: 28HP

Liczba opakowań: 1

Wykończenie: Anodyzowany

Długość: 147.32mm

Materiał: Aluminium

Rodzina produktów: EuropacPRO

Typ produktu: Szyna pozioma

Typ: Wzmocnione, LD

Współpracuje z: Stojaki podrzędne

Waga netto: 0.09kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address.

parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Marki w naszej ofercie:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE