


# Szyna pozioma, przód, typ R-LD, Wytrzymała, Długa krawędź, 40 km



Combinations of horizontal rails and side panels

„+“ = can be combined, „-“ = combination not recommended

|                                                                              | Light = L | Plush = F | Heavy = H | Exaggerated = B |
|------------------------------------------------------------------------------|-----------|-----------|-----------|-----------------|
| Horizontal rail                                                              | +         | +         | +         | +               |
| Horizontal rail with side panel                                              | +         | +         | +         | +               |
| Horizontal rail with side panel and side panel                               | +         | +         | +         | +               |
| Horizontal rail with side panel and side panel and side panel                | +         | +         | +         | +               |
| Horizontal rail with side panel and side panel and side panel and side panel | +         | +         | +         | +               |

Side panel

## NUMER KATALOGOWY

### 34566-340

Wytrzymała szyna pozioma może wytrzymać wstrząsy i wibracje do 25 g. umożliwia stosowanie uchwyty IEE.

## FUNKCJE

Wzmocnione szyny poziome typu R-LD z mocowaniem 3-otworowym zwiększają wytrzymałość

Do wkładania/ekstrakcji płyt CompactPCI lub VME64x

Z urządzeniami HP drukowanymi od 28 km do góry

Długość 20, 28, 40, 42, 63, 84 HP lub 1000 mm

Wyłaczanie aluminium, anodowane wykończenie, przewodząca powierzchnia kontaktowa, z oznaczeniami HP



## ATRYBUTY PRODUKTU

Szerokość stojaka: 40HP

Liczba opakowań: 1

Wykończenie: Anodowany

Długość: 208.28mm

Materiał: Aluminium

Rodzina produktów: EuropacPRO

Typ produktu: Szyna pozioma

Typ: Wzmocnione, LD

Współpracuje z: Stojaki podrzędne

Waga brutto: 0.131kg

\*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

## OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie [www.nvent.com](http://www.nvent.com) oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



©2026 nVent. Wszystkie znaki i logo nVent są własnością firmy nVent Services GmbH albo jej spółek zależnych lub są licencjonowane. Wszystkie pozostałe znaki towarowe są własnością odpowiednich właścicieli. Firma nVent zastrzega sobie prawo do zmiany specyfikacji bez powiadomienia.

Ten dokument jest generowany przez system.