

Improved nVent CADDY Cat HP J-Hook with Pin Driven Angle Bracket



The Improved nVent CADDY Cat HP J-Hook with Pin Driven Angle Bracket is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Pin Driven Angle Bracket attachment. The Assembly simplifies cable management by offering rapid attachment to various surfaces such as concrete, steel or metal decking. This solution is designed to fit a variety of pin drivers, ensuring job site flexibility.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

CARACTERÍSTICAS

Longer leg angle bracket for tool clearance

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro	Area	Cable Capacity, Cat 5e
CAT16HPAFAB3	181009	Aço	Pregalvanized	25 mm	690mm ²	20
CAT21HPAFAB4	181192	Aço	Pregalvanized	33.3 mm	1174mm ²	50
CAT21HPAFAB6	181193	Aço	Pregalvanized	33.3 mm	1174mm ²	50

Número de catálogo	Número do artigo	Material	Acabamento	Diâmetro	Area	Cable Capacity, Cat 5e
CAT32HPAFAB6	181013	Aço	Pregalvanized	50 mm	2561mm ²	90
CAT48HPAFAB6	181235	Aço	Pregalvanized	75 mm	5974mm ²	200
CAT64HPAFAB6	181225	Aço	Pregalvanized	100 mm	9987mm ²	330
CAT21HPAFAB3	181191	Aço	Pregalvanized	33.3 mm	1174mm ²	50
CAT32HPAFAB3	181011	Aço	Pregalvanized	50 mm	2561mm ²	90
CAT32HPAFAB4	181012	Aço	Pregalvanized	50 mm	2561mm ²	90
CAT48HPAFAB3	181233	Aço	Pregalvanized	75 mm	5974mm ²	200
CAT48HPAFAB4	181234	Aço	Pregalvanized	75 mm	5974mm ²	200
CAT64HPAFAB3	181223	Aço	Pregalvanized	100 mm	9987mm ²	330
CAT64HPAFAB4	181224	Aço	Pregalvanized	100 mm	9987mm ²	330

Table 2/2

Número de catálogo	Número do artigo	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Tamanho do orifício	Static Load
CAT16HPAFAB3	181009	15	10	4 mm	270N
CAT21HPAFAB4	181192	40	25	6 mm	270N
CAT21HPAFAB6	181193	40	25	9 mm	270N
CAT32HPAFAB6	181013	60	35	9 mm	270N
CAT48HPAFAB6	181235	150	80	9 mm	270N
CAT64HPAFAB6	181225	220	140	9 mm	270N
CAT21HPAFAB3	181191	40	25	4 mm	270N
CAT32HPAFAB3	181011	60	35	4 mm	270N
CAT32HPAFAB4	181012	60	35	6 mm	270N
CAT48HPAFAB3	181233	150	80	4 mm	270N
CAT48HPAFAB4	181234	150	80	6 mm	270N
CAT64HPAFAB3	181223	220	140	4 mm	270N
CAT64HPAFAB4	181224	220	140	6 mm	270N

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

+1 800 753 9221

Opção 1 – Apoio ao cliente

Opção 2 – Assistência
técnica

Europa

Países Baixos:

+31 800-0200135

França:

+33 800 901 793

Europa

Alemanha:

800 1890272

Outros países:

+31 13 5835404

APAC

Xangai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

